


REV. 0  
DCO 143159

COIL: @ 25°C  
 RESISTANCE 850 OHMS ±10%  
 NOMINAL VOLTAGE 12.0 VDC  
 MUST OPERATE 7.0 VDC  
 MUST RELEASE 4.0 VDC MAX., 0.64 VDC MIN.

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C  
 NOTES: OPERATE TIME 4.0 MS MAX.  
RELEASE TIME 2.0 MS MAX.  
CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO  
1A 28 VDC RESISTIVE 100,000  
OPERATIONS

DR. B.D. 8/17/01 CK *[Signature]* 8/22/01

**CII Technologies™**  
 advanced control electronic solutions

CUST. OPL  
 CUST. NO. M39016/J1-043P REV. \_\_\_\_\_

"JMS" RELAY

JMSC-12XPS