



## KPSI 330

- ◆ Submersible level transducer
- ◆ Small bore, 0.75" diameter
- ◆  $\pm 0.10\%$  FSO static accuracy
- ◆ Two year warranty

The KPSI 330 is a submersible hydrostatic level transducer specifically designed for small bore applications and to meet the rigorous environments encountered in ground water level measurements. This transducer provides repeatable, precision depth measurement under most adverse conditions.

Every KPSI Transducer utilizes a highly accurate pressure sensor assembly specifically designed for hostile fluids and gases. The assembly is integrated with supporting electronics in a durable waterproof housing constructed of 316 stainless steel or titanium. The attached electrical cable is custom manufactured and includes para-aramid synthetic fiber members to prevent errors due to cable elongation, and a unique water block feature that self-seals in the event of accidental cuts to the cable. Each vented reference transducer is shipped with our SuperDry Vent Filter that prevents moisture from entering the vent tube for at least one year without maintenance, even in the most humid environments.

### Features

- ◆ Custom polyurethane or ETFE cable lengths
- ◆ Welded 316SS or titanium body
- ◆ Custom level ranges up to 700 ft. (210 m) H<sub>2</sub>O
- ◆ Multiple analog outputs
- ◆ Ported nose cap
- ◆ Optional lifetime lightning protection
- ◆ Available molded cable seal

### Applications


- ◆ Surface water monitoring
- ◆ Well monitoring
- ◆ Groundwater monitoring
- ◆ Pump control
- ◆ Slug tests
- ◆ Level control
- ◆ Ballast tank control

### Specifications

PARAMETER	COMMENT	
<b>LEVEL RANGES</b>		
Full scale level ranges (Intermediate level ranges are available)	5 thru 700 ft. H <sub>2</sub> O, (1.5 thru 210 m H <sub>2</sub> O)	Vented gage reference
	35 thru 700 ft. H <sub>2</sub> O, (10 thru 210 m H <sub>2</sub> O)	Sealed gage reference
	35 thru 700 ft. H <sub>2</sub> O, (10 thru 210 m H <sub>2</sub> O)	Absolute gage reference
Proof pressure	1.5 x FS	
Burst pressure	2.0 x FS	


<b>STATIC PERFORMANCE</b>		
Static accuracy (Combined effects of non-linearity, hysteresis and repeatability, best fit straight line method)	±0.10% FSO	BFSL method
Resolution	+0.0001% FS	
<b>ENVIRONMENTAL</b>		
Wetted materials	316 SS or titanium; FKM; Polyurethane or ETFE	
Compensated temp range	0 to 50°C	
Thermal error (Maximum allowable deviation from the Best Fit Straight Line due to a change in temperature)	±0.05% FSO/°C, ±0.1% FSO/°C	Worse case over compensated temperature range for ranges < 12 ft. (4 m) H <sub>2</sub> O
Operating temp range	-20 to 60 °C	When attached to polyurethane cable
Protection rating	IP 68, NEMA 6P	
<b>ELECTRICAL</b>		
Excitation	9-28V – VDC output 9-28V – mA output 15-28V – VDC output 10-28V – VDC output	0-5 V, 0-2.5 V, 0-4 V 4-20 0-10 V 1.5-7.5 V
Input current	20 mA max., 3.5 mA max.	For mA output, for VDC output
Output	4-20 mA, 0-5 VDC, 0-2.5 VDC, 0-4 VDC, 0-10 VDC, 1.5-7.5 VDC	For ranges < 5 ft. (1.5 m) H <sub>2</sub> O, only 4-20mA output is available
Zero offset	±0.25 mA for mA output < 0.25 VDC for VDC output	
Output impedance	See loop diagram for mA output 20 ohm for VDC output	
Insulation resistance	100 mega ohm at 50 VDC	
Circuit protection	Polarity, surge/shorted output	
<b>CERTIFICATIONS</b>		
	CE compliant	EN 61326-1:2013 and 61326-2-3:2013
	UL, CUL and FM	Class I, II, III, Div. 1, Groups A,B,C,D,E,F&G
	WEEE/RoHS	Waste from Electrical and Electronic Equipment (WEEE) and Restrictions on the use of Hazardous Substances (RoHS)
<b>PHYSICAL</b>		
Approximate weight	0.47 lbs. (224 g) transducer 0.05 lbs./ft. (79 g/m) cable	
Cable jacket material	Polyurethane (Standard), ETFE (Optional)	
Cable pull strength	200 lbs. (90 kg)	Polyurethane
Cable number of conductors	4	
Cable conductor size	22 AWG	
Cable seal	Molded polyurethane FKM gland	For polyurethane cable For ETFE cable
<b>LIGHTNING PROTECTION</b> (Power supply needs to be limited to 150mA to avoid lock up of the gas tube after a suppression event)		
Life expectancy	>1,000 Operations	
Peak clamping voltage	36 volts	
Response time	<10 nsecs	
Shunts	20,000 amperes	

Dimensions



\* ADD 5.00" FOR LIGHTNING PROTECTION OPTION

Molded Cable Seal Configuration for Polyurethane Cable




\* ADD 5.00" FOR LIGHTNING PROTECTION OPTION

Gland Cable Seal Configuration for ETFE Cable

Electrical Termination / Loop Resistance

ELECTRICAL TERMINATION		
22AWG CONDUCTORS IN A SHIELDED CABLE WITH VENT TUBE		
4-20 mA	RED BLACK	+ EXCITATION - EXCITATION
0-5 VDC	RED BLACK WHITE	+ EXCITATION - EXCITATION + SIGNAL
ALL	DRAIN WIRE	SHIELD



Ordering Information

MODEL		SUBMERSIBLE LEVEL TRANSDUCER	
3	3	0	±0.10% FSO Static Accuracy
↓	↓	↓	
<b>MATERIAL</b>			
S	Stainless Steel		
T	Titanium		
↓			
<b>REFERENCE FORMAT</b>			
1	Vented gage		
3	Sealed gage		
4	Absolute		
↓			
<b>OUTPUT</b>			
3	0-5 VDC		
F	0-2.5 V		
G	0-4 V		
H	0-10 V		
J	1.5-7.5V		
4	4-20 mA		
↓			
<b>PRESSURE CONNECTION</b>			
B	Ported nose cap		
↓			
<b>ELECTRICAL CONNECTION</b>			
0	Molded cable seal		
A	Gland cable seal		
↓			
<b>LIGHTNING PROTECTION</b>			
A	None		
B	Full Lightning Protection		
↓			
<b>LEVEL RANGE (at MAX output)<sup>1</sup></b>			
#	#	#	#
↓	↓	↓	↓
<b>LEVEL RANGE (at MIN output)<sup>1</sup></b>			
#	#	#	#
↓	↓	↓	↓
<b>MOISTURE PROTECTION</b>			
A	None (sealed/absolute only)		
B	Vent Filter		
D	Stainless Steel Vent Filter		
↓			
<b>CABLE TYPE</b>			
1	Polyurethane		
2	ETFE (Electrical Connection "A" Only)		
↓			
<b>CABLE LENGTH</b>			
#	#	#	#
↓	↓	↓	↓
<b>LABEL<sup>2</sup></b>			
A	psi		
B	ft H <sub>2</sub> O		
C	m H <sub>2</sub> O		
↓			
3	3	0	B

**Notes:**

- The part number requires two level range limits, corresponding to the maximum and minimum analog outputs of the transducer, to be specified in **pounds per square inch (psi)** to three decimal places. The lower level range is typically 000.000 unless otherwise required. For reverse output requirements, enter the lower level range for the maximum output signal and the upper range for the minimum output. Use the following conversion factors: **Ft. H<sub>2</sub>O / 2.3073 = psi // m H<sub>2</sub>O / 0.703265 = psi**  
**Examples:** 10 ft. H<sub>2</sub>O / 2.3073 = 4.334 psi (Enter 004.334 in the part number), 10 m H<sub>2</sub>O / 0.703265 = 14.219 psi (Enter 014.219 in the part number)  
 For sealed gage reference add local atmosphere when converting to psi. Contact PSI for assistance.  
**Example:** 10 ft. H<sub>2</sub>O / 2.3073 + 14.7 = 19.034 psi (Enter 019.034 in the part number)
- Units of measure on standard MEAS label. Contact Measurement Specialties if private labeling is required.

**NORTH AMERICA**

Measurement Specialties, Inc.,  
 a TE Connectivity company  
 Tel : 1-800-522-6752  
 Email: [customercare.hmpt@te.com](mailto:customercare.hmpt@te.com)

**EUROPE**

Measurement Specialties (Europe), Ltd.,  
 a TE Connectivity company  
 Tel : +33 (0) 800-440-5100  
 Email: [customercare.dtm@te.com](mailto:customercare.dtm@te.com)

**ASIA**

Measurement Specialties (China), Ltd.,  
 a TE Connectivity company  
 Tel : +86 755 3330 5088  
 Email: [customercare.shzn@te.com](mailto:customercare.shzn@te.com)

**te.com/sensorsolutions**

Measurement Specialties Inc., a TE Connectivity company.  
 Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.  
 The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.  
 © 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

