

RAYCHEM CABLE CLAMPS SINGLE

KEY FEATURES

- Range accepts cable diameters from 15-106mm
- Single level or stackable configurations
- Captive elastomeric inserts for increased cable protection and containment
- Patented slider plate design maximises clamp performance when under shock load
- 33% glass fibre reinforced polyamide resin,
 UV stabilised, selfextinguishing, impact resistant material

Raychem cable clamps have been designed such that the bottom half of the cable clamp can be mounted in position before positioning the cables. The cables can then be aligned and located in the bottom half of the clamp prior to tightening. Other clamps require the cables to be positioned at the same time as the clamp itself, which is difficult to achieve, especially in vertical applications.

Elastomeric inserts are provided with all clamps. This ensures excellent mechanical performance in particular under fault conditions. It also maximises cable contact, even on "non-round" cables, as is the case on many 3 core cable designs which tend to be more "tri-round".

Raychem cable clamps are optimised for harsh environments with stainless steel hardware and self-extinguishing, UV stabilised materials.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



RAYCHEM SINGLE CABLE CLAMPS

more details.


Raychem Single Cable Clamps are available as single clamps with or without hardware, and as a double stacked configuration. Furthermore, TE Connectivity's in-house design team is on hand to produce tailor made schematics and specify technical details for custom cable clamp layouts that suit your specific needs. Please contact your local TE Connectivity Representative for

TE Part Number	Min Cable Ø mm (in)	Max Cable Ø mm (in)	Width A mm (in)	Depth B mm (in)	Bolt Hole Ctrs C mm (in)	Installed Height H - Max mm (in)	Bolt Ø	Туре
CC15-26-SN-M10	15	26	90	60	60	75	M10	Strut Nut
CC15-26-SN-M12	(0.59)	(1.02)	(3.54)	(2.36)	(2.36)	(2.95)	M12	Strut Nut
CC26-38-SN-M10	26	38 (1.5)	90 (3.54)	60 (2.36)	60 (2.36)	75 (2.95)	M10	Strut Nut
CC26-38-SN-M12	(1.02)						M12	Strut Nut
CC38-50-PL-M12	38	50 (1.97)	104 (4.09)	60 (2.36)	75 (2.95)	100 (3.94)	M12	Slider Plate
CC38-50-SN-M12	(1.5)						M12	Strut Nut
CC50-60-PL-M12	50	60 (2.36)	133 (5.24)	60 (2.36)	100 (3.94)	116 (4.57)	M12	Slider Plate
CC50-60-SN-M12	(1.97)						M12	Strut Nut
CC60-70-PL-M12	60	70 (2.76)	146 (5.75)	70 (2.76)	114 (4.49)	130 (5.12)	M12	Slider Plate
CC60-70-SN-M12	(2.36)						M12	Strut Nut
CC68-81-PL-M12	68	81		70 (2.76)	114 (4.49)	130 (5.12)	M12	Slider Plate
CC68-81-SN-M12	(2.68)	(3.19)					M12	Strut Nut
CC80-92-PL-M12	80	92	176	75	142	155 (6.1)	M12	Slider Plate
CC80-92-SN-M12	(3.15)	(3.62)	(6.93)	(2.95)	(5.59)		M12	Strut Nut
CC92-106-PL-M12	92	106 (4.17)	176 (6.93)	75 (2.95)	142 (5.59)	155	M12	Slider Plate
C92-106-SN-M12	(3.62)					(6.1)	M12	Strut Nut

SINGLE LEVEL CLAMPS WITHOUT HARDWARE ORDERING INFORMATION											
Min Cable Ø	Max Cable Ø	Width A	Depth B	Bolt Hole Ctrs C	Installed Height H - Max	Bolt Ø					
26	38	90	60	60	75	M10					
38	50	104	60	75	100	M12					
50	60	133	60	100	130	M12					
60	70	146	70	114	130	M12					
68	81	146	70	114	130	M12					
80	92	176	75	142	155	M12					
92	106	176	75	142	155	M12					
	Min Cable Ø 26 38 50 60 68 80	Min Cable Max Cable 26 38 38 50 50 60 60 70 68 81 80 92	Min Cable Max Cable Width A 26 38 90 38 50 104 50 60 133 60 70 146 68 81 146 80 92 176	Min Cable Max Cable Width A Depth B 26 38 90 60 38 50 104 60 50 60 133 60 60 70 146 70 68 81 146 70 80 92 176 75	Min Cable Max Cable Width A Depth B Bolt Hole Ctrs C 26 38 90 60 60 38 50 104 60 75 50 60 133 60 100 60 70 146 70 114 68 81 146 70 114 80 92 176 75 142	Min Cable Max Cable Width A Depth B Ctrs C Bolt Hole L Ctrs C Installed Height H - Max 26 38 90 60 60 75 38 50 104 60 75 100 50 60 133 60 100 130 60 70 146 70 114 130 68 81 146 70 114 130 80 92 176 75 142 155					




SLIDER PLATE VERSION Used where access to the end of the mounting rail is achievable




VERSION
Used where
access to the end
of the mounting
rail is not possible



NSW/QLD/NT/ACT: +61 (2) 9554 2695 VIC/TAS/SA: +61 (3) 9271 5243 WA: +61 (8) 9358 7806 New Zealand: +64 (9) 634 4580 Email: marketingANZ@te.com







©2016 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2211-DDS01-AU-5/16-EN-CC-Raychem Cable Clamps (CC)

Utilux, TE Connectivity and TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.