

UTILUX COPPER CRIMP BARRIER LINKS CKB TYPE

KEY FEATURES

- For use with oil filled cables
- Solid drawn copper rod
- Electro tinned
- Solid centre barriers

Utilux is a brand that has built an enviable reputation for high quality, reliable electrical connectors. For over 90 years, this dynamic Australian brand has been a leader in the field of interconnection systems.

Our aim is to provide the best possible products and services to keep our customers at the cutting edge of industry standards - internationally.

You can be sure that Utilux branded products are fabricated from the finest materials and produced to exacting tolerances. They represent the latest technology and the best design for the tasks they are required to perform.

Utilux is a leading brand of electrical connectors sold to original equipment manufacturers and electrical distribution companies throughout Australia, New Zealand and Asia. A comprehensive range, the most up to date production technology and the highest quality control standards ensure that there are Utilux connectors, of optimum reliability and durability, for all major power distribution applications.


As part of the worlds largest electrical connector company, TE Connectivity, the development of products is an ongoing commitment. It is done on a global basis, utilising the talents of many people throughout the organisation to ensure a global product for a local market.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

UTILUX COPPER CRIMP BARRIER LINKS



Utilux has engineered the correct combination of material thickness and crimp die selection to ensure that the optimum compression ratios are achieved when crimping. Annealing also ensures that connectors can be crimped without damage and electro tinning minimises corrosion. These features combined with correct termination procedures will ensure a connection that will perform for many years.



PRODUCT SELECTION INFORMATION					
Catalogue Number	Conductor Area (mm ²)	Stranding Metric	Dimensions (mm)		Crimping Die
			A	G	
CKB10	10	7/1.35	48	4.7	38-57CU
CKB16	16	7/1.70	45	5.5	38-63CU
CKB20	20	7/2.14	45	6.3	38-70CU
CKB25	25	19/1.35	48	7.1	38-77CU
CKB35	35	19/1.53	48	8.4	38-92CU
CKB50	50	19/1.78	54	9.5	38-104CU
CKB70	70	19/2.14	51	11.0	38-115CU
CKB95	95	37/1.78	54	13.4	38-142CU
CKB120	120	37/2.03	76	15.5	38-165CU
CKB150	150	37/2.25	76	16.3	38-183CU
CKB185	185	37/2.52	88	18.4	38-200CU
CKB240	240	61/2.25	76	21.2	38-231CU
CKB300	300	61/2.52	88	23.8	38-260CU
CKB400	400	61/2.85	89	26.9	40-281CU
CKB500	500	61/3.20	145	30.0	40-310CU
CKB630	630	127/2.52	145	33.5	40-370CU

te.com/energy

©2016 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2487-DDS10-AU-3/16

Utilux, TE Connectivity and TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Customer Support Centers

NSW/QLD/NT/ACT: +61 (2) 9554 2695
 VIC/TAS/SA: +61 (3) 9271 5243
 WA: +61 (8) 9358 7806
 New Zealand: +64 (9) 634 4580