




TOLERANCES
 XX = ±.03
 XXX = ±.010

M4 X .7 STUD (2X)
 DIN 6798A LOCK WASHER (2X)
 DIN 934 NUT HEX (4X)

INCLUDE SEPARATELY
 MIL-C-39029/22-192
 CONTACTS (5X)
 FOR THESE TERMINALS




REV. B
 DCO 301098

COIL: @ 25°C	
RESISTANCE	290 OHMS ±10%
NOMINAL VOLTAGE	28.0 VDC
MUST OPERATE	18.0 VDC MAX.
MUST RELEASE	7.0 VDC MAX. 1.5 VDC MIN.

ENVIRONMENT:	
VIBRATION	75 Hz TO 3000 Hz @ 20 g's
SHOCK	50 g's 11 MS. DURATION
TEMPERATURE	-70 °C TO +125 °C
NOTES: OPERATE AND RELEASE 15 ms MAX. AT 25 °C	
CONTACT BOUNCE 1 ms MAX. AUX BOUNCE 5ms MAX	
DIELECTRIC 1250 VRMS MAX./60 Hz (1000 VRMS/60 Hz COIL TO CASE)	
COIL TRANSIENT SUPPRESSION 42 VDC MAX.	

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	
	50 AMPS 28 VDC, 115 VAC/400 Hz
	AUX 2 AMP 28VDC, 115VAC/400Hz
	RESISTIVE 50,000 OPERATIONS EACH

DR. B.D. 19JAN2009 CK. O.DARBY 1/21/09

Tyco Electronics ©COPYRIGHT 2005
 TYCO ELECTRONICS CORPORATION
 ALL INTERNATIONAL RIGHTS RESERVED

CUST. CATALOG ITEM
 CUST. NO. REV.

TE NUMBER
 3-1617800-0

CII PART NUMBER
 FCAC-150-KR4A