



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Product Compliance Engineer																											
Company Unique ID	485203835	Response Date	2014-07-25	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1-102153-2	Amount	13271.0270208	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true																																	
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	102129-2				64.0	51.8597972	mg																										
Material	2	Nickel Plate				64.0	1.03	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	64.0	0.00206	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	64.0	0.00103	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	64.0	1.02691	mg																										
Material	2	Gold Plate				64.0	0.043016	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	64.0	0.04288695	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	64.0	1.2905E-4	mg																										
Material	2	Tin-Lead Plate				64.0	0.27	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	64.0	0.0189	mg																										
Substance	3	Tin	Supplier	7440-31-5	92.3	64.0	0.24921	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	64.0	0.00189	mg																										
Material	2	Brass				64.0	50.46	mg																										
Substance	3	Tin	Supplier	7440-31-5	0.1	64.0	0.05046	mg																										
Substance	3	Copper	Supplier	7440-50-8	64.0	64.0	32.2944	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	64.0	0.02523	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	64.0	0.005046	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	64.0	5.046E-4	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	64.0	0.05046	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.1	64.0	0.05046	mg																										
Substance	3	Zinc	Supplier	7440-66-6	35.2085	64.0	17.76621	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	64.0	0.005046	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	64.0	0.005046	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.05	64.0	0.02523	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.3	64.0	0.15138	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	64.0	2.523E-4	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	64.0	0.005046	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	64.0	0.02523	mg																										

Material	2	Gold Plate				64.0	0.0567812	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	64.0	1.7034E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	64.0	0.05661086	mg	
Sub-Item	1	1-102142-3				1.0	9952.0	mg	
Material	2	PBT-GF30FR(17)				1.0	9952.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	2985.6	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	3284.16	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	99.52	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	99.52	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	497.6	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	2985.6	mg	