Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Penica, John R	**Contact Title**	Sr Mgr Engineering
Company Unique ID	TE Connectivity	**Response Date**	2017-10-05	**Contact Email**	jrpenica@te.com		
Contact Phone Number		+1-717-592-3266					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1-1571983-3	**Amount**	0.303	**Version**	-	**Identity**	
Manufacturer Item Name	GDH10S04=DIP SWITCH	**Weight Uom**	g	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Movable Contact - Au Plating				1.0	1.0E-4	g	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	1.0E-4	g	
Material	1	Movable Contact - Nickel Plating				1.0	1.0E-4	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	1.0E-4	g	
Material	1	COVER - PPS				1.0	0.09	g	
Substance	2	Carbon black	Supplier	1333-86-4	64.5	1.0	0.05805	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	0.0315	g	
Substance	2	Poly(thio-1,4-phenylene)	Supplier	25212-74-2	0.5	1.0	4.5E-4	g	
Material	1	Fixed plat - Au Plating				1.0	4.0E-4	g	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	4.0E-4	g	
Material	1	CASE - PPS				1.0	0.1	g	
Substance	2	Carbon black	Supplier	1333-86-4	64.5	1.0	0.0645	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	0.035	g	
Substance	2	Poly(thio-1,4-phenylene)	Supplier	25212-74-2	0.5	1.0	5.0E-4	g	
Material	1	Movable Contact				1.0	0.0198	g	
Substance	2	Copper	Supplier	7440-50-8	99.6	1.0	0.0197208	g	
Substance	2	Titanium	Supplier	7440-32-6	0.4	1.0	7.92E-5	g	
Material	1	Fixed plat - Nickel Plating				1.0	4.0E-4	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	4.0E-4	g	
Material	1	Fixed plate - Phosphor Bronze				1.0	0.0722	g	
Substance	2	Tin	Supplier	7440-31-5	8.0	1.0	0.005776	g	
Substance	2	Phosphorus	Supplier	7723-14-0	0.25	1.0	1.805E-4	g	
Substance	2	Zinc	Supplier	7440-66-6	0.18	1.0	1.2996E-4	g	
Substance	2	Iron	Supplier	7439-89-6	0.09	1.0	6.498E-5	g	
Substance	2	Copper	Supplier	7440-50-8	91.26	1.0	0.06588972	g	
Substance	2	Nickel	Nickel	7440-02-0	0.18	1.0	1.2996E-4	g	

Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.04	1.0	2.888E-5	g	
Material	1	Knod (Actuator) - LCP				1.0	0.02	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	0.0050	g	
Substance	2	1,4-Benzenedicarboxylic acid, polymer with 1,2-ethanediol and 4-hydroxybenzoic acid	Supplier	25822-54-2	75.0	1.0	0.015	g	