Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Chan, Nelson	**Contact Title**	Manager Sales, HKG SELL DIR-EMS
Company Unique ID	TE Connectivity	**Response Date**	2016-05-27	**Contact Email**	nelson.chan@te.com		
Contact Phone Number		852-2738-8751					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1-1761685-3	**Amount**	6410.203632	**Version**	-	**Identity**	
Manufacturer Item Name	IDC LOW PRO HDR 40P VERT SHT LAT	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Manufacturing Information							
J-STD-020 MSL Rating		**Max Total a Wave Time**		**Ramp Rate**		**Wave Additional Info**	
Classification Temp		**Max Wave Solder Time**	10.0	**Ramp Down Rate**		**Psl Rating Reflow**	
Max Time Within 5		**Psl Rating Wave**		**Package Designator**		**Size**	0.0
Time Above 217		**Reflow Additional Info**		**Preheat Max Temp**		**Terminal Base Alloy**	NAC
Preheat Duration		**bulk Solder Termination**	NAC	**Nbr or Reflow Cycles**		**Terminal Plating**	NAC
Preheat Min Temp		**Nbr of Instances**	0	**Component Temp Spike**		**Shape**	NAC

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	D3685-40=BASE,CONN,L/P,EJECT.H				1.0	4234.0	mg	
Material	2	PBT-GF30				1.0	4234.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1270.2	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	54.4	1.0	2303.296	mg	
Substance	3	C.I. Pigment Green 7	Supplier	1328-53-6	0.1	1.0	4.234	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.5	1.0	148.19	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylidene)bis[(2,6-dibromo-4,1-phenylene)oxymethylene]]bis[oxirane]	Supplier	68928-70-1	12.0	1.0	508.08	mg	
Sub-Item	1	0K19301=EJECTOR RETAINER				2.0	475.0	mg	
Material	2	PBT-GF30				2.0	475.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	2.0	142.5	mg	

Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	54.4	2.0	258.4	mg	
Substance	3	C.I. Pigment Green 7	Supplier	1328-53-6	0.1	2.0	0.475	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.5	2.0	16.625	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylidene)bis[(2,6-dibromo-4,1-phenylene)oxymethylene]]bis[oxirane]	Supplier	68928-70-1	12.0	2.0	57.0	mg	
Sub-Item	1	IDC BANDOLIER POST 30 DPLX				40.0	30.6550908	mg	
Material	2	Gold Plate				40.0	0.0861541	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.08589564	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	2.5846E-4	mg	
Material	2	Gold Plate				40.0	0.0775387	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	2.3262E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.07730608	mg	
Material	2	Tin Plate				40.0	0.161248	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	3.225E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	40.0	0.16081	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	40.0	1.1287E-4	mg	
Material	2	Phos Bronze				40.0	29.87	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	40.0	2.987E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	40.0	0.0044805	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	40.0	0.005974	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	40.0	0.10454	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	0.002987	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	40.0	1.73246	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	40.0	0.02987	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	40.0	0.08961	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	40.0	27.81898	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	40.0	0.002987	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	40.0	0.02987	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	40.0	0.02987	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	40.0	0.002987	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	1.4935E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	0.014935	mg	
Material	2	Nickel Plate				40.0	0.46015	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	9.203E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	4.6015E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	0.45877	mg	