



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	TE Connectivity	Response Date	2016-08-04	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1-2178615-4	Amount	910.0	Version	-	Identity																												
Manufacturer Item Name	RCPT,2MM,14P, R ANG MT,8AU,3.ST	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Gold plating				1.0	4.0	mg																										
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	4.0	mg																										
Material	1	Tin plating				1.0	3.0	mg																										
Substance	2	Tin	Supplier	7440-31-5	99.8	1.0	2.994	mg																										
Substance	2	Copper	Supplier	7440-50-8	0.2	1.0	0.0060	mg																										
Material	1	C5191R-H				1.0	492.0	mg																										
Substance	2	Copper	Supplier	7440-50-8	93.47	1.0	459.8724	mg																										
Substance	2	Iron	Supplier	7439-89-6	0.03	1.0	0.1476	mg																										
Substance	2	Zinc	Supplier	7440-66-6	0.1	1.0	0.492	mg																										
Substance	2	Phosphorus	Supplier	7723-14-0	0.12	1.0	0.5904	mg																										
Substance	2	Tin	Supplier	7440-31-5	6.25	1.0	30.75	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.03	1.0	0.1476	mg																										
Material	1	CH 230NK				1.0	408.0	mg																										
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	122.4	mg																										
Substance	2	Carbon black	Supplier	1333-86-4	1.0	1.0	4.08	mg																										
Substance	2	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	25.0	1.0	102.0	mg																										
Substance	2	1,4-Benzenedicarboxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	44.0	1.0	179.52	mg																										
Material	1	Nickel plating				1.0	3.0	mg																										
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	3.0	mg																										