Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer
Company Unique ID	485203835	Response Date	2013-12-05	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	1-5206478-2	Amount	11800.7576	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	205716-1				1.0	284.0	mg	
Material	2	FOAMING AGENT				1.0	2.84	mg	
Substance	3	Octadecanoic acid	Supplier	57-11-4	0.05	1.0	0.00142	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-hydro-.omega.-hydroxy-	Supplier	25322-68-3	0.05	1.0	0.00142	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-(1-oxooctadecyl)-.omega.-[(1-oxooctadecyl)oxy]-	Supplier	9005-08-7	0.65	1.0	0.01846	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	88.0	1.0	2.4992	mg	
Substance	3	Diazene-1,2-dicarboxamide (C,C-azodi(formamide))	Supplier	123-77-3	10.0	1.0	0.284	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	1.0	0.0284	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-(1-oxooctadecyl)-.omega.-hydroxy-	Supplier	9004-99-3	0.25	1.0	0.0071	mg	
Material	2	PP				1.0	281.16	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	11.2464	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.0	1.0	2.8116	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	5.6232	mg	
Substance	3	Polypropylene - ISO 1043-1 Term PP	Supplier	1043-1-PP	86.0	1.0	241.7976	mg	
Substance	3	Benzene, 1,1-(1-methylethylidene)bis[3,5-dibromo-4-(2,3-dibromopropoxy)-	Brominated Flame Retardants (other than PBBs or PBDEs)	21850-44-2	7.0	1.0	19.6812	mg	

Sub-Item	1	5205979-1				2.0	450.6173	mg	
Material	2	Carbon Steel				2.0	444.0	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	2.0	0.1776	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0444	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	2.0	436.22334	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0444	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.444	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	2.0	0.222	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00444	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	2.0	1.0212	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	2.0	0.666	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	2.0	4.44	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.0444	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.00222	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.444	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.222	mg	
Material	2	Tri Chrome Film				2.0	0.0173	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.01038	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	10.0	2.0	0.00173	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.00519	mg	
Material	2	Zinc Plate				2.0	6.6	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	6.6	mg	
Sub-Item	1	5023529-2				1.0	1383.685	mg	
Material	2	Carbon Steel				1.0	1367.043	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	1.0	0.54682	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1367	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	1.0	1343.09924	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1367	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.36704	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	1.0	0.68352	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01367043	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	1.0	3.1442	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	2.05056	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	1.0	13.67043	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.1367	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00683522	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.36704	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.68352	mg	
Material	2	Zinc Plate				1.0	16.61	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	1.0	16.61	mg	
Material	2	Tri Chrome Film				1.0	0.032	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	1.0	0.0096	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	10.0	1.0	0.0032	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	1.0	0.0192	mg	
Sub-Item	1	5749314-2				2.0	981.076	mg	
Material	2	Carbon Steel				2.0	967.247	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	2.0	0.3869	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0967247	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	2.0	950.30567	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0967247	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.96725	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	2.0	0.48362	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00967247	mg	

Substance	3	Carbon	Supplier	7440-44-0	0.23	2.0	2.22467	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	2.0	1.45087	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	2.0	9.67247	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.0967247	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.00483624	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.96725	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.48362	mg	
Material	2	Zinc Plate				2.0	13.802	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	13.802	mg	
Material	2	Tri Chrome Film				2.0	0.027	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.0081	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	10.0	2.0	0.0027	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.0162	mg	
Sub-Item	1	206389-1				1.0	6524.468	mg	
Material	2	FOAMING AGENT				1.0	65.24468	mg	
Substance	3	Octadecanoic acid	Supplier	57-11-4	0.05	1.0	0.03262234	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-hydro-.omega.-hydroxy-	Supplier	25322-68-3	0.05	1.0	0.03262234	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-(1-oxooctadecyl)-.omega.-[(1-oxooctadecyl)oxy]-	Supplier	9005-08-7	0.65	1.0	0.42409	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	88.0	1.0	57.41532	mg	
Substance	3	Diazene-1,2-dicarboxamide (C,C-azodi(formamide))	Supplier	123-77-3	10.0	1.0	6.52447	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	1.0	0.65245	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-(1-oxooctadecyl)-.omega.-hydroxy-	Supplier	9004-99-3	0.25	1.0	0.16311	mg	
Material	2	PP				1.0	6459.22332	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	258.36893	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.0	1.0	64.59223	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	129.18447	mg	
Substance	3	Polypropylene - ISO 1043-1 Term PP	Supplier	1043-1-PP	86.0	1.0	5554.93206	mg	
Substance	3	Benzene, 1,1-(1-methylethylidene)bis[3,5-dibromo-4-(2,3-dibromopropoxy)-	Brominated Flame Retardants (other than PBBs or PBDEs)	21850-44-2	7.0	1.0	452.14563	mg	
Sub-Item	1	5017363-1				1.0	276.818	mg	
Material	2	Carbon Steel				1.0	270.829	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	1.0	0.10833	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0270829	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	1.0	266.08543	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0270829	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.27083	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	1.0	0.13541	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00270829	mg	

Substance	3	Carbon	Supplier	7440-44-0	0.23	1.0	0.62291	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	0.40624	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	1.0	2.70829	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0270829	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00135414	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.27083	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.13541	mg	
Material	2	Zinc Plate				1.0	5.977	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	1.0	5.977	mg	
Material	2	Tri Chrome Film				1.0	0.012	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	1.0	0.0036	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	10.0	1.0	0.0012	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	1.0	0.0072	mg	
Sub-Item	1	748274-2				2.0	234.2	mg	
Material	2	Stainless Steel				2.0	234.2	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.02342	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.35	2.0	0.8197	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.002342	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.0	2.0	2.342	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	2.0	4.684	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.05	2.0	0.1171	mg	
Substance	3	Chromium	Supplier	7440-47-3	19.0	2.0	44.498	mg	
Substance	3	Iron	Supplier	7439-89-6	66.4885	2.0	155.71607	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	2.0	0.3513	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.8	2.0	1.8736	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	2.0	0.07026	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.02342	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.02342	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.001171	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	2.0	23.42	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.2342	mg	