Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	John R Penica	Contact Title	Sr Mgr Environmental Engineering
Company Unique ID	TE Connectivity	Response Date	2015-12-22	Contact Email	jrpenica@te.com		
Contact Phone Number		+1-717-592-3266					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	1-827314-9	Amount	1.4755286	Version	-	Identity	
Manufacturer Item Name	19P MOD2 STIFT LEI	Weight Uom	g	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MOD2STGH,1RH,50P,SW				0.38	1.1613	g	
Material	2	PCT-GF20				0.38	1.1613	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.318	0.38	0.00369293	g	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	0.38	0.023226	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.212	0.38	0.00246196	g	
Substance	3	2,4,8,10-Tetraoxa-3,9-diphosphaspiro[5.5]undecane, 3,9-bis[2,4-bis(1,1-dimethylethyl)phenoxy]-	Supplier	26741-53-7	0.3	0.38	0.0034839	g	
Substance	3	Poly(oxy-1,2-ethanediyl),a-(1-oxododecyl)-w-[(1-oxododecyl)oxy]-	Supplier	9005-02-1	4.3	0.38	0.0499359	g	
Substance	3	Ethene, homopolymer, oxidized	Supplier	68441-17-8	0.5	0.38	0.0058065	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	0.38	0.011613	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	19.0	0.38	0.220647	g	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	18.0	0.38	0.209034	g	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	4.5	0.38	0.0522585	g	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2-[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-2-(hydroxymethyl)-1,3-propanediyl] ester	Supplier	84633-54-5	0.0030	0.38	3.4839E-5	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedimethanol	Supplier	25135-20-0	49.0	0.38	0.569037	g	
Substance	3	Formaldehyde, polymer with 2-(chloromethyl)oxirane and 2-methylphenol	Supplier	29690-82-2	0.57	0.38	0.00661941	g	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.297	0.38	0.00344906	g	
Sub-Item	1	MOD2 STIFTE MAGAZ				19.0	0.0544334	g	
Material	2	Phos Bronze				19.0	0.05309	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	19.0	5.309E-6	g	
Substance	3	Copper	Supplier	7440-50-8	91.9385	19.0	0.04881015	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	19.0	5.309E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	19.0	1.5927E-4	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	19.0	1.0618E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	19.0	5.309E-7	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	19.0	5.309E-5	g	
Substance	3	Tin	Supplier	7440-31-5	7.0	19.0	0.0037163	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	19.0	1.8581E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	19.0	7.9635E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	19.0	5.309E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	19.0	2.6545E-7	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	19.0	2.6545E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	19.0	5.309E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	19.0	2.6545E-5	g	
Material	2	Tin Plate				19.0	9.1E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	19.0	6.37E-7	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	19.0	1.82E-6	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	19.0	9.0754E-4	g	
Material	2	Nickel Plate				19.0	4.334E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	19.0	8.668E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	19.0	4.334E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	19.0	4.321E-4	g	