Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Adrian, Bernd	**Contact Title**	Sr R&D/Product Dvl Engineer, Product Development
Company Unique ID	TE Connectivity	**Response Date**	2017-06-07	**Contact Email**	bernd.adrian@te.com		
Contact Phone Number		+431905601813					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1393774-8	**Amount**	1826.4	**Version**	-	**Identity**	
Manufacturer Item Name	V23026A1002B201	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Flublech				1.0	259.5	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.012	1.0	0.03114	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.017	1.0	0.044115	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.0501	1.0	0.13001	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.03	1.0	0.07785	mg	
Substance	2	Iron	Supplier	7439-89-6	99.7487	1.0	258.84788	mg	
Substance	2	Carbon	Supplier	7440-44-0	0.027	1.0	0.070065	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.025	1.0	0.064875	mg	
Substance	2	Copper	Supplier	7440-50-8	0.0401	1.0	0.10406	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.0501	1.0	0.13001	mg	
Material	1	coil wire				1.0	592.8	mg	
Substance	2	Acetic acid, 2-methylpropyl ester	Supplier	110-19-0	0.8288	1.0	4.91313	mg	
Substance	2	Copper	Supplier	7440-50-8	96.6848	1.0	573.14749	mg	
Substance	2	Ethanol	Supplier	64-17-5	0.3315	1.0	1.96513	mg	
Substance	2	Stoddard solvent	Supplier	8052-41-3	0.0829	1.0	0.49143	mg	
Substance	2	Naphtha (petroleum), hydrotreated light	Supplier	64742-49-0	0.8288	1.0	4.91313	mg	
Substance	2	2-Propanol	Supplier	67-63-0	0.3315	1.0	1.96513	mg	
Substance	2	Solvent naphtha (petroleum), light arom.	Supplier	64742-95-6	0.0829	1.0	0.49143	mg	
Substance	2	Acetic acid, butyl ester	Supplier	123-86-4	0.8288	1.0	4.91313	mg	
Material	1	casing				1.0	144.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	43.2	mg	
Substance	2	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	70.0	1.0	100.8	mg	
Material	1	insulating foil				1.0	7.0	mg	
Substance	2	PMF (polyimide)	Supplier	60842-76-4	69.2683	1.0	4.84878	mg	

Substance	2	2-Propenoic acid, homopolymer, sodium salt	Supplier	9003-04-7	30.7317	1.0	2.15122	mg	
Material	1	Flux Pin				1.0	0.2	mg	
Substance	2	2-Propanol	Supplier	67-63-0	70.0	1.0	0.14	mg	
Substance	2	Rosin	Supplier	8050-09-7	30.0	1.0	0.06	mg	
Material	1	epoxy resin				1.0	332.8	mg	
Substance	2	Poly(oxy-1,4-butanediyl), .alpha.-(2-oxiranylmethyl)-.omega.-(2-oxiranylmethoxy)-	Supplier	26951-52-0	10.0	1.0	33.28	mg	
Substance	2	Formaldehyde, polymer with 2-(chloromethyl)oxirane and phenol	Supplier	9003-36-5	21.5	1.0	71.552	mg	
Substance	2	Zinc-borate	Supplier	51201-70-8	47.0	1.0	156.416	mg	
Substance	2	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2-(chloromethyl)oxirane	Supplier	25068-38-6	21.5	1.0	71.552	mg	
Material	1	hardener				1.0	14.0	mg	
Substance	2	Cyclohexanemethanamine, 5-amino-1,3,3-trimethyl-	Supplier	2855-13-2	100.0	1.0	14.0	mg	
Material	1	pole plate(steel)				1.0	84.4	mg	
Substance	2	Carbon	Supplier	7440-44-0	0.0269	1.0	0.0227036	mg	
Substance	2	Iron	Supplier	7439-89-6	99.0808	1.0	83.6242	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.0119	1.0	0.0100436	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.0497	1.0	0.0419468	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.0249	1.0	0.0210156	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.1691	1.0	0.14272	mg	
Substance	2	Copper	Supplier	7440-50-8	0.0398	1.0	0.0335912	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.0298	1.0	0.0251512	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.5671	1.0	0.47863	mg	
Material	1	epoxy resin thread bond				1.0	3.0	mg	
Substance	2	Formaldehyde, polymer with 2-(chloromethyl)oxirane and phenol	Supplier	9003-36-5	60.0	1.0	1.8	mg	
Substance	2	2-Propenoic acid, 2-methyl-, polymer with butyl 2-propenoate and methyl 2-methyl-2-propenoate	Supplier	25035-69-2	35.0	1.0	1.05	mg	
Substance	2	Guanidine, N-cyano-	Supplier	461-58-5	5.0	1.0	0.15	mg	
Material	1	Contact spring (steel)				1.0	57.6	mg	
Substance	2	Nickel	Nickel	7440-02-0	45.0	1.0	25.92	mg	
Substance	2	Iron	Supplier	7439-89-6	55.0	1.0	31.68	mg	
Material	1	solder				1.0	0.2	mg	
Substance	2	Tin	Supplier	7440-31-5	99.7	1.0	0.1994	mg	
Substance	2	Copper	Supplier	7440-50-8	0.3	1.0	6.0E-4	mg	
Material	1	coil conductor				1.0	44.2	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.4863	1.0	0.21494	mg	
Substance	2	Tin	Supplier	7440-31-5	5.9708	1.0	2.63909	mg	
Substance	2	Copper	Supplier	7440-50-8	93.5429	1.0	41.34596	mg	
Material	1	Pole plate Coating				1.0	5.4	mg	
Substance	2	Rhodium	Supplier	7440-16-6	0.6149	1.0	0.0332046	mg	
Substance	2	Palladium	Supplier	7440-05-3	4.0248	1.0	0.21734	mg	
Substance	2	Gold	Supplier	7440-57-5	10.0416	1.0	0.54225	mg	
Substance	2	Nickel	Nickel	7440-02-0	85.3187	1.0	4.6072054	mg	
Material	1	solenoid				1.0	90.1	mg	
Substance	2	Iron strontium oxide (Fe12SrO19)	Supplier	12023-91-5	100.0	1.0	90.1	mg	
Material	1	color				1.0	0.2	mg	

Substance	2	Solvent naphtha (petroleum), light arom.	Supplier	64742-95-6	17.5	1.0	0.035	mg	
Substance	2	Fatty acids, castor-oil, caustic-oxidized, distn. residues, esters with 1,3-butanediol	Supplier	113669-95-7	26.25	1.0	0.0525	mg	
Substance	2	Cyclohexanone	Supplier	108-94-1	37.5	1.0	0.075	mg	
Substance	2	2-Pentanone, 4-hydroxy-4-methyl-	Supplier	123-42-2	6.25	1.0	0.0125	mg	
Substance	2	Ethanol, 2-butoxy-, 1-acetate	Supplier	112-07-2	6.25	1.0	0.0125	mg	
Substance	2	Acetic acid, 2-hydroxy-, butyl ester	Supplier	7397-62-8	6.25	1.0	0.0125	mg	
Material	1	Flux coil				1.0	0.2	mg	
Substance	2	Rosin	Supplier	8050-09-7	1.0	1.0	0.0020	mg	
Substance	2	2-Propanol	Supplier	67-63-0	94.0	1.0	0.188	mg	
Substance	2	Butanedioic acid	Supplier	110-15-6	5.0	1.0	0.01	mg	
Material	1	Contact spring coating				1.0	4.4	mg	
Substance	2	Copper	Supplier	7440-50-8	73.6298	1.0	3.23971	mg	
Substance	2	Palladium	Supplier	7440-05-3	3.3218	1.0	0.14616	mg	
Substance	2	Gold	Supplier	7440-57-5	2.4701	1.0	0.10868	mg	
Substance	2	Rhodium	Supplier	7440-16-6	0.0958	1.0	0.0042152	mg	
Substance	2	Nickel	Nickel	7440-02-0	20.4825	1.0	0.90123	mg	
Material	1	coil bobbin				1.0	186.4	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	55.92	mg	
Substance	2	Fatty acids, castor-oil, caustic-oxidized, distn. residues, esters with 1,3-butanediol	Supplier	113669-95-7	70.0	1.0	130.48	mg	