Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	TE Product Compliance	**Contact Title**	-
Company Unique ID	TE Connectivity	**Response Date**	2018-09-03	**Contact Email**	productcompliance@te.com		
Contact Phone Number	+001-800-522-6752						

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1487595-3	**Amount**	42269.425	**Version**	-	**Identity**	
Manufacturer Item Name	USB, A-B, 28/26, BLACK, .83M	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	USB 2.0 CBL 1P*28#+2C*26 # BK01				1.0	21489.3	mg	
Material	2	Conductor				1.0	8602.2	mg	
Substance	3	Tin	Supplier	7440-31-5	2.0	1.0	172.044	mg	
Substance	3	Copper	Supplier	7440-50-8	98.0	1.0	8430.156	mg	
Material	2	Jacket				1.0	1474.2	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	1.65	1.0	24.3243	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	41.41	1.0	610.46622	mg	
Substance	3	Carbonic acid calcium salt (1:1)	Supplier	471-34-1	24.81	1.0	365.74902	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	2.47	1.0	36.41274	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 1,2-diisononyl ester	Phthalates (DINP, DIDP, DNOP)	28553-12-0	29.66	1.0	437.24772	mg	
Material	2	Insulation				1.0	10084.5	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	1.65	1.0	166.39425	mg	
Substance	3	Carbonic acid calcium salt (1:1)	Supplier	471-34-1	24.81	1.0	2501.96445	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	2.47	1.0	249.08715	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	41.41	1.0	4175.99145	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 1,2-diisononyl ester	Phthalates (DINP, DIDP, DNOP)	28553-12-0	29.66	1.0	2991.0627	mg	
Material	2	HD-PE				1.0	842.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	8.424	mg	

Substance	3	Ethene, homopolymer	Supplier	9002-88-4	99.0	1.0	833.976	mg	
Material	2	Al/PET				1.0	486.0	mg	
Substance	3	Acetic acid ethyl ester	Supplier	141-78-6	0.1	1.0	0.486	mg	
Substance	3	Aluminum	Supplier	7429-90-5	60.0	1.0	291.6	mg	
Substance	3	Poly(oxy-1,2-ethanediyloxycarbonyl-1,4-phenylenecarbonyl)	Supplier	25038-59-9	35.0	1.0	170.1	mg	
Substance	3	1,2-Ethanediol	Supplier	107-21-1	4.8	1.0	23.328	mg	
Substance	3	2-Methylpentane-2,4-diol	Supplier	107-41-5	0.1	1.0	0.486	mg	
Sub-Item	1	SOLDER BAR,Sn99.3/Cu0.7				1.0	150.0	mg	
Material	2	Solder Bar				1.0	150.0	mg	
Substance	3	Tin	Supplier	7440-31-5	99.3	1.0	148.95	mg	
Substance	3	Copper	Supplier	7440-50-8	0.7	1.0	1.05	mg	
Sub-Item	1	Other Consumer Cable Assy's				1.0	12000.0	mg	
Material	2	MOLDED BLOCK				1.0	12000.0	mg	
Substance	3	Carbonic acid calcium salt (1:1)	Supplier	471-34-1	22.81	1.0	2737.2	mg	
Substance	3	Antimony oxide	Supplier	1327-33-9	0.73	1.0	87.6	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	51.86	1.0	6223.2	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	3.11	1.0	373.2	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.73	1.0	87.6	mg	
Substance	3	1,2,4-Benzenetricarboxylic acid, 1,2,4-tris(2-ethylhexyl) ester	Supplier	3319-31-1	18.68	1.0	2241.6	mg	
Substance	3	Soybean oil, epoxidized	Supplier	8013-07-8	2.08	1.0	249.6	mg	
Sub-Item	1	USB 4P GOLD 30U B TYPE				1.0	4200.0	mg	
Material	2	Shell-Ni plating				1.0	0.6	mg	
Substance	3	Nickel	Nickel	7440-02-0	100.0	1.0	0.6	mg	
Material	2	Housing				1.0	1000.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	43.0	1.0	430.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	300.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	70.0	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylidene)bis[(2,6-dibromo-4,1-phenylene)oxymethylene]]bis[oxirane]	Supplier	68928-70-1	20.0	1.0	200.0	mg	
Material	2	Contact				1.0	366.4	mg	
Substance	3	Copper	Supplier	7440-50-8	65.14	1.0	238.67296	mg	
Substance	3	Iron	Supplier	7439-89-6	0.0070	1.0	0.025648	mg	
Substance	3	Zinc	Supplier	7440-66-6	34.851	1.0	127.69406	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0020	1.0	0.007328	mg	
Material	2	Shell				1.0	2832.4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.19	1.0	5.38156	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.018	1.0	0.50983	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.0030	1.0	0.084972	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.012	1.0	0.33989	mg	
Substance	3	Iron	Supplier	7439-89-6	99.777	1.0	2826.08375	mg	
Material	2	Contact-Au plating				1.0	0.3	mg	

Substance	3	Gold	Supplier	7440-57-5	100.0	1.0	0.3	mg	
Material	2	Contact-Pd-Ni plating				1.0	0.3	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	1.0	0.06	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	1.0	0.24	mg	
Sub-Item	1	USB A TYPE 4PIN MALE GOLD30U				1.0	4080.0	mg	
Material	2	Shell-Ni plating				1.0	0.6	mg	
Substance	3	Nickel	Nickel	7440-02-0	100.0	1.0	0.6	mg	
Material	2	Housing				1.0	400.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	43.0	1.0	172.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	120.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	28.0	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylidene)bis[(2,6-dibromo-4,1-phenylene)oxymethylene]]bis[oxirane]	Supplier	68928-70-1	20.0	1.0	80.0	mg	
Material	2	Contact				1.0	49.4	mg	
Substance	3	Copper	Supplier	7440-50-8	65.14	1.0	32.17916	mg	
Substance	3	Iron	Supplier	7439-89-6	0.0070	1.0	0.003458	mg	
Substance	3	Zinc	Supplier	7440-66-6	34.851	1.0	17.21639	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0020	1.0	9.88E-4	mg	
Material	2	Shell				1.0	3549.4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.19	1.0	6.74386	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.018	1.0	0.63889	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.0030	1.0	0.10648	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.012	1.0	0.42593	mg	
Substance	3	Iron	Supplier	7439-89-6	99.777	1.0	3541.48484	mg	
Material	2	Contact-Au plating				1.0	0.3	mg	
Substance	3	Gold	Supplier	7440-57-5	100.0	1.0	0.3	mg	
Material	2	Contact-Pd-Ni plating				1.0	0.3	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	1.0	0.06	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	1.0	0.24	mg	
Material	2	Cover				1.0	80.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	40.0	1.0	32.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	24.0	mg	
Substance	3	Carbon black	Supplier	1333-86-4	3.0	1.0	2.4	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylidene)bis[(2,6-dibromo-4,1-phenylene)oxymethylene]]bis[oxirane]	Supplier	68928-70-1	20.0	1.0	16.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	5.6	mg	
Sub-Item	1	COPER FOIL TAPE 6W				1.0	100.125	mg	
Material	2	Copper				1.0	86.3478	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.0431739	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	86.26145	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.05	1.0	0.0431739	mg	
Material	2	Glue				1.0	13.7772	mg	
Substance	3	2-Propenoic acid, homopolymer	Supplier	9003-01-4	100.0	1.0	13.7772	mg	

Sub-Item	1	LABEL, 25.4X35.05MM				1.0	50.0	mg	
Material	2	Ink				1.0	15.0	mg	
Substance	3	Cyclosiloxanes, di-Me	Supplier	69430-24-6	30.0	1.0	4.5	mg	
Substance	3	Rutile (TiO2)	Supplier	1317-80-2	30.0	1.0	4.5	mg	
Substance	3	Cyclohexanone	Supplier	108-94-1	20.0	1.0	3.0	mg	
Substance	3	2-Propenoic acid	Supplier	79-10-7	20.0	1.0	3.0	mg	
Material	2	PS Adhesive Materials				1.0	35.0	mg	
Substance	3	Water	Supplier	7732-18-5	1.0	1.0	0.35	mg	
Substance	3	Poly(oxy-1,2-ethanediyloxycarbonyl-1,4-phenylenecarbonyl)	Supplier	25038-59-9	26.0	1.0	9.1	mg	
Substance	3	2-Propenoic acid, polymer with butyl 2-propenoate, 2-ethylhexyl 2-propenoate and methyl 2-propenoate	Supplier	98060-25-4	14.0	1.0	4.9	mg	
Substance	3	Pulp, cellulose	Supplier	65996-61-4	58.0	1.0	20.3	mg	
Substance	3	Siloxanes and Silicones, di-Me, vinyl group-terminated	Supplier	68083-19-2	1.0	1.0	0.35	mg	
Sub-Item	1	SOLDER WIRE,LEAD-FREE,SN99.3 CU0.7% 0.8				1.0	200.0	mg	
Material	2	Solder wire				1.0	200.0	mg	
Substance	3	Copper	Supplier	7440-50-8	0.7	1.0	1.4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.3	1.0	198.6	mg	