


COIL: @ 25°C
 RESISTANCE _____ 63 OHMS \pm 10%
 NOMINAL VOLTAGE _____ 5.0 VDC
 MUST OPERATE VOLTAGE _____ 3.0 VDC
 TURN-ON BASE CURRENT _____ 0.60 mADC
 MUST RELEASE _____ 1.7 VDC MAX, 0.24 VDC MIN.

ENVIRONMENT:
 VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ TURN-ON TIME 2.0 MS MAX
 _____ TURN-OFF TIME 7.5 MS MAX
 _____ CONTACT STABILIZATION TIME 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: _____ LOW LEVEL TO 1A
 _____ 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 9/29/98 *OK. JERRY 9/29/98*



CUST. _____ QPL
 CUST. NO. M28776/5-025M

TYPE J1MAT RELAY

J1MACT-5XM