


REV. 0
DCO 143304

COIL: @ 25°C	
RESISTANCE	2000 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	14.2 VDC
MUST RELEASE	8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	OPERATE TIME 2.0 MS MAX.
	RELEASE TIME 4.0 MS MAX.
	CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	LOW LEVEL TO 1A
	28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 11/13/01

Handwritten signature 11/13/01

CII Technologies
advanced control electronic solutions

CUST. OPL
CUST. NO. M39016/23-024P REV. _____

"JIMAD" RELAY

J1MAPD-26XP