Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	John R. Penica	**Contact Title**	Manager Environmental Engineering
Company Unique ID	485203835	**Response Date**	2014-05-05	**Contact Email**	jrpenica@te.com		
Contact Phone Number	717-592-3266						

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1676386-1	**Amount**	4.75	**Version**	-	**Identity**	
Manufacturer Item Name		**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						
EUREACH-0613	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Ceramic				1.0	4.49	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	96.0	1.0	4.3104	mg	N/A
Substance	2	Silica	Supplier	7631-86-9	4.0	1.0	0.1796	mg	N/A
Material	1	Silver C3 paste				1.0	0.066	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	0.066	mg	N/A
Material	1	Silver C1 Paste				1.0	0.0518	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	0.0518	mg	N/A
Material	1	Nickel plating				1.0	0.013	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.013	mg	N/A
Material	1	Epoxy Resin (G2 layer)				1.0	0.043	mg	
Substance	2	Propanoic acid, 2-methyl-, monoester with 2,2,4-trimethyl-1,3-pentanediol	Supplier	25265-77-4	100.0	1.0	0.043	mg	N/A
Material	1	Tin plating				1.0	0.03	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.03	mg	N/A
Material	1	Epoxy Ink (G Mark)				1.0	0.024	mg	
Substance	2	Ethanol, 2-butoxy-	Supplier	111-76-2	100.0	1.0	0.024	mg	N/A
Material	1	NiCr				1.0	0.0322	mg	
Substance	2	Nickel	Nickel	7440-02-0	50.0	1.0	0.0161	mg	N/A
Substance	2	Chromium	Supplier	7440-47-3	50.0	1.0	0.0161	mg	N/A