



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	485203835	Response Date	2013-10-28	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1857995-1	Amount	17082.909	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	1-1645385-3				25.0	383.398	mg																										
Material	2	Tin Plate				25.0	0.35	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	25.0	3.4965E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	25.0	0.34965	mg																										
Material	2	Nickel Plate				25.0	3.0	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	25.0	0.0060	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	25.0	0.0030	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	25.0	2.991	mg																										
Material	2	Phos Bronze				25.0	240.0	mg																										
Substance	3	Copper	Supplier	7440-50-8	94.6835	25.0	227.2404	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	25.0	0.048	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	25.0	0.024	mg																										
Substance	3	Tin	Supplier	7440-31-5	4.5	25.0	10.8	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	25.0	0.036	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	25.0	0.24	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	25.0	0.024	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	25.0	0.0024	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	25.0	0.72	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	25.0	0.24	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	25.0	0.24	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	25.0	0.024	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	25.0	0.12	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	25.0	0.24	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	25.0	0.0012	mg																										
Material	2	PBT-GF20				25.0	140.0	mg																										
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	56.5	25.0	79.1	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	25.0	4.2	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	25.0	28.0	mg																										

Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	25.0	7.0	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	25.0	0.7	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	15.0	25.0	21.0	mg	
Material	2	LUBRICANT, H M-15+.03 UV TRACER				25.0	0.01	mg	
Substance	3	Fatty acids, C18-unsatd., dimers, bis(2-ethylhexyl) esters	Supplier	68424-40-8	14.2	25.0	0.00142	mg	
Substance	3	Sulfonic acids, petroleum, barium salts	Supplier	61790-48-5	63.9	25.0	0.00639	mg	
Substance	3	White mineral oil (petroleum)	Supplier	8042-47-5	14.2	25.0	0.00142	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	7.7	25.0	7.7E-4	mg	
Material	2	Palladium-Nickel Plate				25.0	0.011	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	25.0	0.0088	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	25.0	0.0022	mg	
Material	2	Gold Plate				25.0	0.027	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.026919	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	25.0	8.1E-5	mg	
Sub-Item	1	994433-3				1.0	0.08	mg	
Material	2	444PC DOUBLE COATED TAPE				1.0	0.08	mg	
Substance	3	Poly(oxy-1,2-ethanedioxy carbonyl-1,4-phenylene carbonyl)	Supplier	25038-59-9	15.0	1.0	0.012	mg	
Substance	3	Resin acids and Rosin acids, hydrogenated, esters with glycerol	Supplier	65997-13-9	35.0	1.0	0.028	mg	
Substance	3	2-Propenoic acid, polymer with isooctyl 2-propenoate	Supplier	9017-68-9	50.0	1.0	0.04	mg	
Sub-Item	1	646342-1				1.0	4317.0	mg	
Material	2	PBT-GF20				1.0	4317.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	56.5	1.0	2439.105	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	129.51	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	863.4	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	215.85	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	21.585	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	15.0	1.0	647.55	mg	
Sub-Item	1	9-5338109-2				1.0	3180.879	mg	
Material	2	Tin Plate				1.0	0.468	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	4.6753E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.46753	mg	

Material	2	Nickel Plate				1.0	7.995	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.01599	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.007995	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	7.97102	mg	
Material	2	Phos Bronze				1.0	3172.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	3003.36062	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.6344	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.3172	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	142.74	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.4758	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	3.172	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.3172	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.03172	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	9.516	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	3.172	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.172	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.3172	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.586	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	3.172	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01586	mg	
Material	2	Gold Plate				1.0	0.416	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.41475	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.001248	mg	