



Applications

- ◆ Groundwater Monitoring
- ◆ Down Hole
- ◆ Surface Water Monitoring
- ◆ Tailrace and Forebay Monitoring
- ◆ Oceanographic Research

Features

- ◆ Custom Polyurethane or ETFE Cable Lengths
- ◆ Welded 316SS or Titanium
- ◆ Custom Level Ranges up to 230 ft. (70m) H₂O
- ◆ Shipped with Long-Life Vent Filter
- * Removable Cable Options including PVC jacketed steel armored cable

KPSI 500

- SDI-12 Submersible Level Transducer
- ±0.05% FS Total Error Band
- Optional Lifetime Lightning Protection
- Two year warranty
- 1" Diameter


The KPSI 500 submersible hydrostatic level transducer represents the leading edge of level sensing technology available today. Incorporating a highly stable media-isolated sensor, the KPSI 500 features SDI-12 and RS-485 serial-digital interface standards. SDI-12 is a commonly used standard for interfacing data recorders with microprocessor-based sensors, in the environmental monitoring field. The KPSI 500 is an excellent solution for applications with requirements that require minimal current drain. It will accommodate cable lengths between sensor and recorder up to 1000 feet.



Specifications

PARAMETER		COMMENT				
LEVEL RANGES						
Full Scale Level Ranges (intermediate level ranges are available)	10 thru 230 ft. (3 thru 70m) $\mathrm{H}_2\mathrm{O}$	Vented Gage Reference				
Proof Pressure	1.5 x FS					
Burst Pressure	2.0 x FS					
STATIC PERFORMANCE (Combined	d Errors Due to Nonlinearity, Hysteresis, Non-repeatability,	and Thermal Effects over the Compensated Temperature Range)				
Level	±0.05% FS TEB ±0.10% FS TEB	For level ranges $>$ 10 ft. (3m) H_2O For level ranges $<=$ 10 ft. (3m) H_2O				
Temperature	+0.5ºC					
Excitation	±0.5 VDC	8 to 28 volts				
Resolution	+0.0001% FS					
MEASUREMENT RESOLUTION						
Level	±0.0001%FS					
Temperature	±0.001°C					
Excitation	±0.1 VDC					
ENVIRONMENTAL						
Wetted Materials	etted Materials 316 SS or Titanium; POM; FKM; polyurethane or ETFE					
Compensated Temp Range	0 to 50°C					
Operating Temp Range	-20 to 60 °C	When attached to polyurethane cable				
Protection Rating	IP 68, NEMA 6P					
ELECTRICAL	·					
Excitation	6-28V – VDC output					
Input Current	8 mA max 1.0 mA	Average current during data acquisition Quiescent				
Interface	SDI-12, version 1.3 RS-485	SDI-12 protocol				
CERTIFICATIONS						
	CE compliant	EN 61326-1:2013 and 61326-2-3:2013				
PHYSICAL						
Approximate Weight	0.75 lbs. (340 g) transducer 0.05 lbs./ft. (79 g/m) cable					
Cable Jacket Material	Polyurethane ETFE					
	Armored polyurethane (optional 859 accessory)	PVC Jacketed steel armored polyurethane				
Cable Pull Strength	200 lbs. (90 kg)	Polyurethane				
Cable Number of Conductors	4					
Cable Conductor Size	22 AWG					
Cable Seal	Molded Polyurethane FKM Gland	For polyurethane cable For ETFE cable				
LIGHTNING PROTECTION (power	supply needs to be limited to 150mA to avoid lock	up of the gas tube after a suppression event)				
Life Expectancy	>1,000 Operations					
Peak Clamping Voltage						
reak Glamping Voltage	36 Volts					
Response Time	36 Volts <10 nsecs					

Dimensions




Electrical Termination and Removable Cable Options

ELECTRICAL TERMINATION								
22AWG CONDUCTORS IN A SHIELDED CABLE WITH VENT TUBE								
	RED	+ SUPPLY						
SDI-12	BLACK	- SUPPLY						
	WHITE	SIGNAL						
	RED	+ SUPPLY						
RS-485	BLACK	- SUPPLY						
NO-400	WHITE	RS485-A						
	GREEN	RS485-B						
ALL	DRAIN WIRE	SHIELD						

	MOD	EL	REMOVABLE CABLE							
8	5	9								
1	\downarrow	1	MATERIAL							
			S	Stainless Steel						
			Т	T Titanium						
			\downarrow	OUTPUT						
				С	SDI-1	SDI-12				
				D	RS 485 w/SDI-12 protocol					
				\downarrow	ELEC	ELECTRICAL CONNECTION				
					0	Molded cable seal				
					Α	Gland cable seal				
					\downarrow	CABLE TYPE				
						1 Polyurethane				
						2 ETFE (Connection A Only)				
						4 Armored (Connection O Only; 200 Feet Max)				
	Į					1	CABLE LENGTH			
							#	#	#	(in feet)
8	5	9								

Ordering Information



Notes:

- The part number requires two level range limits, corresponding to the maximum and minimum analog outputs of the transducer, to be specified in **pounds per square inch (psi)** to three decimal places. The lower level range is typically 000.000 unless otherwise required. For reverse output requirements, enter the lower level range for the maximum output signal and the upper range for the minimum output. Use the following conversion factors: **Ft. H₂O (2.3073 = psi)** // m **H₂O (0.703265 = psi) Examples:** 10 ft. H₂O (2.3073 = 4.334 psi (Enter 004.334 in the part number), 10 m H₂O (0.703265 = 14.219 psi (Enter 014.219 in the part number)

 For sealed gage reference add local atmosphere when converting to psi. Contact PSI for assistance. **Example:** 10 ft. H₂O (2.3073 + 14.7 = 19.034 psi (Enter 019.034 in the part number)

 Units of measure on standard MEAS label. Contact Measurement Specialties if private labeling is required.
- 2
- Removable / Armored Cable must utilize Electrical Connection R only. Removable / Armored cable must be ordered as separate 859 Removable Cable Assembly Part Number (see guide on page 3).

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity company Tel: 1-800-522-6752

Email: customercare.hmpt@te.com

EUROPE

Measurement Specialties (Europe), Ltd., a TE Connectivity company Tel: +33 (0) 800-440-5100

Email: customercare.dtmd@te.com

ASIA

Measurement Specialties (China), Ltd., a TE Connectivity company Tel: +86 755 3330 5088 Email: customercare.shzn@te.com

te.com/sensorsolutions

Measurement Specialties Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

