Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	JASON KUNTZ	**Contact Title**	Product Compliance Engineer
Company Unique ID	TE Connectivity	**Response Date**	2016-05-31	**Contact Email**	jp.kuntz@te.com		
Contact Phone Number		717-986-5932					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	2-1676913-6	**Amount**	222.0	**Version**	-	**Identity**	
Manufacturer Item Name	YR1 0.1% 1K0	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Tin Plated Copper				1.0	130.0032	mg	
Substance	2	Tin	Supplier	7440-31-5	0.5	1.0	0.65002	mg	N/A
Substance	2	Copper	Supplier	7440-50-8	99.5	1.0	129.35318	mg	N/A
Material	1	Cold Rolled Steel & Tin Plated				1.0	31.9902	mg	
Substance	2	Iron	Supplier	7439-89-6	99.5	1.0	31.83025	mg	N/A
Substance	2	Tin	Supplier	7440-31-5	0.5	1.0	0.15995	mg	N/A
Material	1	Target				1.0	0.1332	mg	
Substance	2	Nickel	Nickel	7440-02-0	80.0	1.0	0.10656	mg	N/A
Substance	2	Chromium	Supplier	7440-47-3	20.0	1.0	0.02664	mg	N/A
Material	1	Alumina				1.0	39.8046	mg	
Substance	2	Barium oxide (BaO)	Supplier	1304-28-5	1.5	1.0	0.59707	mg	N/A
Substance	2	Magnesium oxide (MgO)	Supplier	1309-48-4	0.4	1.0	0.15922	mg	N/A
Substance	2	Calcium oxide (CaO)	Supplier	1305-78-8	1.5	1.0	0.59707	mg	N/A
Substance	2	Silica, vitreous	Supplier	60676-86-0	10.96	1.0	4.36258	mg	N/A
Substance	2	Sodium oxide (NaO)	Supplier	12401-86-4	0.04	1.0	0.01592184	mg	N/A
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	85.0	1.0	33.83391	mg	N/A
Substance	2	Potassium oxide (K2O)	Supplier	12136-45-7	0.2	1.0	0.0796092	mg	N/A
Substance	2	Iron oxide (Fe2O3)	Supplier	1309-37-1	0.4	1.0	0.15922	mg	N/A
Material	1	Epoxy				1.0	20.0688	mg	
Substance	2	Ethanol, 2,2-oxybis-, polymer with 2-(chloromethyl)oxirane	Supplier	25928-94-3	100.0	1.0	20.0688	mg	N/A