Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Rohde, Daniel F.	Contact Title	Prod Sustaining Engineer, A&C Lifecycle Engr
Company Unique ID	TE Connectivity	Response Date	2015-05-02	Contact Email	daniel.rohde@te.com		
Contact Phone Number		+1-717-986-3211					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	2-320568-3	Amount	1919.21375878	Version	-	Identity	
Manufacturer Item Name	TERMINAL,PID G R IR 10 8	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SLEEVE ASSEMBLY 10 IR				1.0	494.27082078	mg	
Material	2	PA66				1.0	192.08795616	mg	
Substance	3	Copper	Supplier	7440-50-8	0.02	1.0	0.03841759	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.1	1.0	2.11297	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	98.78	1.0	189.74448	mg	
Substance	3	Bromine	Supplier	7726-95-6	0.1	1.0	0.19209	mg	
Material	2	Copper				1.0	287.644	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.14382	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.28764	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00287644	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	286.77388	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00287644	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0287644	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0287644	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0575288	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.28764	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00143822	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0287644	mg	
Material	2	COLORANT				1.0	5.94086462	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	2.0	1.0	0.11882	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediyl)]	Supplier	25038-54-4	95.5	1.0	5.67353	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	1.0	0.02970432	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	0.11882	mg	
Material	2	Nickel Plate				1.0	8.598	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.017196	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.008598	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	8.57221	mg	
Sub-Item	1	TERMINAL,SOLIS R 10 8				1.0	1424.942938	mg	
Material	2	Copper				1.0	1406.129	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.70306	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.40613	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.01406129	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	1401.87546	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01406129	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.14061	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.14061	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.28123	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.40613	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00703064	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.14061	mg	
Material	2	Tin Plate				1.0	11.214938	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	11.15886	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.04485975	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.01121494	mg	
Material	2	Brazing Filler				1.0	7.599	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.7	1.0	0.50913	mg	
Substance	3	Copper	Supplier	7440-50-8	87.05	1.0	6.61493	mg	
Substance	3	Silver	Supplier	7440-22-4	6.25	1.0	0.47494	mg	