Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance
Company Unique ID	485203835	Response Date	2013-12-30	Contact Email	jrpenica@te.com		
Contact Phone Number		717-592-3266					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	1-826634-0	Amount	1852.4	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Polyester Resin				1.0	516.1	mg	
Material	2	Polyester Compound				1.0	516.1	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	55.0	1.0	283.855	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	5.0	1.0	25.805	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	154.83	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	25.805	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	5.0	1.0	25.805	mg	
Sub-Item	1	9-927949-0				10.0	55.62	mg	
Material	2	Phos Bronze				10.0	54.51	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.005451	mg	
Substance	3	Copper	Supplier	7440-50-8	91.9335	10.0	50.11295	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.005451	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.16353	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.010902	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	5.451E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.05451	mg	
Substance	3	Tin	Supplier	7440-31-5	7.0	10.0	3.8157	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	10.0	0.19078	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	10.0	0.0081765	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.05451	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	2.7255E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.005451	mg	

Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.05451	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.027255	mg	
Material	2	Nickel Plate				10.0	0.57	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	10.0	0.00114	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	5.7E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.56829	mg	
Material	2	Tin Plate				10.0	0.32	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	3.1968E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	0.31968	mg	
Material	2	Gold Plate				10.0	0.22	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.21934	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	6.6E-4	mg	
Sub-Item	1	9-927949-1				10.0	78.01	mg	
Material	2	Phos Bronze				10.0	76.73	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.007673	mg	
Substance	3	Copper	Supplier	7440-50-8	91.9335	10.0	70.54057	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.007673	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.23019	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.015346	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	7.673E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.07673	mg	
Substance	3	Tin	Supplier	7440-31-5	7.0	10.0	5.3711	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	10.0	0.26856	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	10.0	0.0115095	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.07673	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	3.8365E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.007673	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.07673	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.038365	mg	
Material	2	Nickel Plate				10.0	0.74	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	10.0	0.00148	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	7.4E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.73778	mg	
Material	2	Tin Plate				10.0	0.32	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	3.1968E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	0.31968	mg	
Material	2	Gold Plate				10.0	0.22	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.21934	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	6.6E-4	mg	