Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Penica, John R	**Contact Title**	Sr Mgr Environmental Engineering, IND Central Eng
Company Unique ID	TE Connectivity	**Response Date**	2015-12-09	**Contact Email**	jrpenica@te.com		
Contact Phone Number		+1-717-592-3266					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1-87230-3	**Amount**	2709.6031834	**Version**	-	**Identity**	
Manufacturer Item Name	26 MODII HDR DRRA UNSHRD .100	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Manufacturing Information							
J-STD-020 MSL Rating		**Max Total a Wave Time**		**Ramp Rate**		**Wave Additional Info**	
Classification Temp		**Max Wave Solder Time**	10.0	**Ramp Down Rate**		**Psl Rating Reflow**	
Max Time Within 5		**Psl Rating Wave**		**Package Designator**		**Size**	0.0
Time Above 217		**Reflow Additional Info**		**Preheat Max Temp**		**Terminal Base Alloy**	NAC
Preheat Duration		**bulk Solder Termination**	NAC	**Nbr or Reflow Cycles**		**Terminal Plating**	NAC
Preheat Min Temp		**Nbr of Instances**	0	**Component Temp Spike**		**Shape**	NAC

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MOD II POST PLTD 15 SEL				13.0	82.0226609	mg	
Material	2	Phos Bronze				13.0	80.943	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	13.0	76.65181	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	13.0	0.0161886	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.0080943	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	13.0	3.64244	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	13.0	0.00404715	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	13.0	0.080943	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.0080943	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	8.0943E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	13.0	0.24283	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	13.0	0.080943	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.080943	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	13.0	0.00404715	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.0404715	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	13.0	0.080943	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	4.0471E-4	mg	
Material	2	Nickel Plate				13.0	0.975	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.00195	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	9.75E-4	mg	

Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.97207	mg	
Material	2	Gold Plate				13.0	0.0207882	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	13.0	2.07882E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.9	13.0	0.02076741	mg	
Material	2	Gold Plate				13.0	0.0838727	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.08362108	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	13.0	2.5162E-4	mg	
Sub-Item	1	Nylon Compound				1.0	815.72	mg	
Material	2	(PA6+PA66)-GF20				1.0	815.72	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	40.786	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.04	1.0	0.32629	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	16.3144	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.040786	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.0	1.0	154.9868	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	22.0	1.0	179.4584	mg	
Substance	3	Polyamide Polymer Blend - ISO 1043-1 Term PA66+PA6	Supplier	1043-1-PA66+PA6	51.949	1.0	423.75838	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0060	1.0	0.0489432	mg	
Sub-Item	1	MOD II POST PLTD 15 SEL				13.0	63.6606609	mg	
Material	2	Phos Bronze				13.0	62.8	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	13.0	59.47066	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	13.0	0.01256	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.00628	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	13.0	2.826	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	13.0	0.00314	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	13.0	0.0628	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.00628	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	6.28E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	13.0	0.1884	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	13.0	0.0628	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.0628	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	13.0	0.00314	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.0314	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	13.0	0.0628	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	3.14E-4	mg	
Material	2	Nickel Plate				13.0	0.756	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.001512	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	7.56E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.75373	mg	
Material	2	Gold Plate				13.0	0.0207882	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	13.0	2.07882E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.9	13.0	0.02076741	mg	
Material	2	Gold Plate				13.0	0.0838727	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.08362108	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	13.0	2.5162E-4	mg	