Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer
Company Unique ID	485203835	Response Date	2014-05-15	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	2198236-1	Amount	43319.89	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	2169315-3				6.0	1801.1	mg	
Material	2	Nickel Plate				6.0	1.1	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	2.0E-4	6.0	1.0E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	5.0E-4	6.0	1.0E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	83.9989	6.0	0.92396	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	16.0	6.0	0.176	mg	
Substance	3	Chromium	Supplier	7440-47-3	2.0E-4	6.0	1.0E-5	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	2.0E-4	6.0	1.0E-5	mg	
Material	2	Aluminum Alloy				6.0	1800.0	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.1	6.0	1.8	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	1.8	mg	
Substance	3	Aluminum	Supplier	7429-90-5	97.3685	6.0	1752.633	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.1	6.0	1.8	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.18	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.018	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.9	6.0	16.2	mg	
Substance	3	Titanium	Supplier	7440-32-6	0.1	6.0	1.8	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.6	6.0	10.8	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	6.0	1.8	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	6.0	6.3	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	6.0	1.8	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.18	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	1.8	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.0090	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	6.0	0.9	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.18	mg	
Sub-Item	1	2149266-2				6.0	686.0	mg	
Material	2	Polycarbonate Compound				6.0	686.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	90.0	6.0	617.4	mg	

Substance	3	Aromatic Brominated flame retardant - ISO 1043-4 code #FR(16)	Supplier	1043-4-FR16	5.0	6.0	34.3	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	5.0	6.0	34.3	mg	
Sub-Item	1	2169259-2				1.0	24305.29	mg	
Material	2	Tin Plate				1.0	88.96	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.08887104	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	88.87113	mg	
Material	2	Phos Bronze				1.0	3130.6	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	2964.16165	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.62612	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.31306	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	140.877	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.46959	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.31306	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	3.1306	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.031306	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	9.3918	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	3.1306	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.1306	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.31306	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.5653	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	3.1306	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.015653	mg	
Material	2	Nickel Alloy				1.0	20860.0	mg	
Substance	3	Copper	Supplier	7440-50-8	56.0	1.0	11681.6	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.2086	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	2.086	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	2.086	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	2.086	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	20.86	mg	
Substance	3	Iron	Supplier	7439-89-6	0.25	1.0	52.15	mg	
Substance	3	Zinc	Supplier	7440-66-6	23.5635	1.0	4915.3461	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.5	1.0	104.3	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	1.043	mg	
Substance	3	Nickel	Nickel	7440-02-0	19.5	1.0	4067.7	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.1043	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	10.43	mg	
Material	2	Lubricant				1.0	116.25	mg	
Substance	3	Naphtha (petroleum), hydrotreated heavy	Supplier	64742-48-9	76.0	1.0	88.35	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	6.5	1.0	7.55625	mg	
Substance	3	White mineral oil (petroleum)	Supplier	8042-47-5	5.5	1.0	6.39375	mg	
Substance	3	Fatty acids, C18-unsatd., dimers, bis(2-ethylhexyl) esters	Supplier	68424-40-8	12.0	1.0	13.95	mg	
Material	2	Nickel Plate				1.0	109.48	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.21896	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.10948	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	109.15156	mg	
Sub-Item	1	2149178-4				6.0	682.0	mg	
Material	2	Stainless Steel				6.0	682.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	18.0	6.0	122.76	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.5	6.0	3.41	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.045	6.0	0.3069	mg	

Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.0682	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.01	6.0	0.0682	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.5	6.0	10.23	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	6.0	1.023	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	6.0	13.64	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.03	6.0	0.2046	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	6.0	0.2046	mg	
Substance	3	Iron	Supplier	7439-89-6	68.6145	6.0	467.95089	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.682	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.0682	mg	
Substance	3	Nickel	Nickel	7440-02-0	9.0	6.0	61.38	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.00341	mg	