Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	JASON KUNTZ	**Contact Title**	Product Compliance Engineer
Company Unique ID	TE Connectivity	**Response Date**	2016-05-19	**Contact Email**	jp.kuntz@te.com		
Contact Phone Number		717-986-5932					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1-966444-0	**Amount**	732.6786	**Version**	-	**Identity**	
Manufacturer Item Name	10P HV100 REC.CON.TE,7.0,DURAGOLD	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	36P HV100 HSG 7.0MM, TAPED				0.277	1433.0	mg	
Material	2	PBT-GF-15				0.277	1433.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	0.277	14.33	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	15.0	0.277	214.95	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	31.25	0.277	447.8125	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	21.5	0.277	308.095	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	31.25	0.277	447.8125	mg	
Sub-Item	1	HV100 CNT U-ED, AU PLATED- PD UNDERPLATE				10.0	33.57376	mg	
Material	2	Gold Plate				10.0	0.043	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.042871	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	10.0	1.29E-4	mg	
Material	2	Phos Bronze				10.0	33.28	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	10.0	31.51566	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.006656	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.003328	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	10.0	1.4976	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	10.0	0.001664	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.03328	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.003328	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	3.328E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.09984	mg	

Substance	3	Phosphorus	Supplier	7723-14-0	0.1	10.0	0.03328	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.03328	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	10.0	0.001664	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.01664	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.03328	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	1.664E-4	mg	
Material	2	Palladium plate				10.0	0.0441	mg	
Substance	3	Palladium	Supplier	7440-05-3	100.0	10.0	0.0441	mg	
Material	2	Gold Plate				10.0	0.00266	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	10.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.00265202	mg	
Material	2	Tin Plate				10.0	0.204	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	4.08E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	10.0	0.20345	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	10.0	1.428E-4	mg	