Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Wu, Cc	**Contact Title**	Engineer Product Compliance china
Company Unique ID	TE Connectivity	**Response Date**	2018-01-28	**Contact Email**	cc.wu@te.com		
Contact Phone Number		86-2124071672					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	3-640477-3	**Amount**	1398.1	**Version**	-	**Identity**	
Manufacturer Item Name	03P MTA156 ASSY ON TAPE LF	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MTA156 CONT 18AWG SN / PHBZ				3.0	209.6	mg	
Material	2	Tin Plate				3.0	4.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.0092	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	4.58758	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	0.00322	mg	
Material	2	Phos Bronze				3.0	203.8	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	3.0	192.99554	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	3.0	0.04076	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	3.0	0.02038	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	3.0	9.171	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	3.0	0.01019	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	3.0	0.2038	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.02038	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	0.002038	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	3.0	0.6114	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	3.0	0.2038	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.2038	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.01019	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.1019	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	3.0	0.2038	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	0.001019	mg	
Material	2	Nickel Plate				3.0	1.2	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.0024	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	0.0012	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	1.1964	mg	

Sub-Item	1	03P MTA156 HSG ORNGE CE W/O LR				1.0	769.3	mg	
Material	2	COLORANT				1.0	15.386	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediyl)]	Supplier	25038-54-4	96.85	1.0	14.90134	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.15	1.0	0.48466	mg	
Material	2	PA66				1.0	753.914	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	99.355	1.0	749.05125	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.0020	1.0	0.01507828	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.3	1.0	2.26174	mg	
Substance	3	Water	Supplier	7732-18-5	0.2	1.0	1.50783	mg	
Substance	3	Aluminum, hydroxybis(octadecanoato-.kappa.O)-	Supplier	300-92-5	0.14	1.0	1.05548	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0030	1.0	0.02261742	mg	