Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china
Company Unique ID	TE Connectivity	Response Date	2016-05-18	Contact Email	cc.wu@te.com		
Contact Phone Number		86-2124071672					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	3-794624-2	Amount	556.461	Version	-	Identity	
Manufacturer Item Name	02P MICRO MNL ASSY,R/A,SMT LF	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Post Contact right angle SMT I				1.0	35.986	mg	
Material	2	Brass				1.0	34.3395	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	3.4339E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	9.62279	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.01716975	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00343395	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.01716975	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0343395	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	24.55274	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	3.4339E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00343395	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.717E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.068679	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00171697	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.01716975	mg	
Material	2	Tin Plate				1.0	1.1295	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	1.12645	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.002259	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	7.9065E-4	mg	
Material	2	Nickel Plate				1.0	0.517	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.001034	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	5.17E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.51545	mg	
Sub-Item	1	MICROMNL LP CONT,R/A,SN				1.0	57.715	mg	
Material	2	Brass				1.0	56.8	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	5.68E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	15.91678	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.0284	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00568	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.0284	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0568	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	40.612	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.68E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00568	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.84E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.1136	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00284	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0284	mg	
Material	2	Tin Plate				1.0	0.157	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.15658	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	3.14E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	1.099E-4	mg	
Material	2	Nickel Plate				1.0	0.758	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.001516	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	7.58E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.75573	mg	
Sub-Item	1	2POS MICRO MNL HSG,BLACK				1.0	236.52	mg	
Material	2	PA4T-GF30-FR(40)				1.0	236.52	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.9	1.0	2.12868	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	70.956	mg	
Substance	3	Polyamide 4T - ISO 1043-1 Term PA4T	Supplier	1043-1-PA4T	47.1	1.0	111.40092	mg	
Substance	3	Halogen-free organic phosphorus flame retradant - ISO 1043-4 code #FR(40)	Supplier	1043-4-FR40	12.0	1.0	28.3824	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	23.652	mg	
Sub-Item	1	MICROMNL LP CONT,R/A,SN				2.0	113.12	mg	
Material	2	Phos Bronze				2.0	110.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.11	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.011	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	2.0	0.22	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	0.0055	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	2.0	99.05335	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.022	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	2.0	0.385	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.0011	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.11	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.011	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	2.0	9.9	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.11	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	5.5E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0055	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.055	mg	
Material	2	Tin Plate				2.0	1.94	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	1.93476	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00388	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.001358	mg	

Material	2	Nickel Plate				2.0	1.18	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00236	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00118	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	1.17646	mg	