Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance
Company Unique ID	TE Connectivity	Response Date	2016-04-21	Contact Email	jrpenica@te.com		
Contact Phone Number		717-592-3266					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	34159	Amount	873.52643	Version	-	Identity	
Manufacturer Item Name	TERMINAL,PG R 16-14 6	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	TERMINAL,BODY RING 16-14 6				1.0	694.32553	mg	
Material	2	Copper				1.0	686.73526	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.34337	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00686735	mg	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	685.06993	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00686735	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.03433676	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.06867353	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.13735	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.68674	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.34337	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00343368	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.03433676	mg	
Material	2	Tin Plate				1.0	7.59027	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	7.56978	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01518054	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.00531319	mg	
Sub-Item	1	Vinyl Compound				1.0	178.3	mg	
Material	2	PVC				1.0	178.3	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	4.0E-4	1.0	7.132E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	7.5	1.0	13.3725	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	87.9961	1.0	156.89705	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	1.5	1.0	2.6745	mg	

Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.5	1.0	0.8915	mg	
Substance	3	Calcium hydroxide (Ca(OH)2)	Supplier	1305-62-0	0.0035	1.0	0.0062405	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[2-[(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.5	1.0	0.8915	mg	
Substance	3	Limestone	Supplier	1317-65-3	2.0	1.0	3.566	mg	
Sub-Item	1	Colorant				1.0	0.9009	mg	
Material	2	COLORANT				1.0	0.9009	mg	
Substance	3	Rosin	Supplier	8050-09-7	0.0090	1.0	8.1081E-5	mg	
Substance	3	Aluminum oxide (Al2O3)	Supplier	1344-28-1	0.5	1.0	0.0045045	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[2-[(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.8	1.0	0.0072072	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	0.8	1.0	0.0072072	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.2	1.0	0.0018018	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	70.0	1.0	0.63063	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.009009	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	11.0	1.0	0.099099	mg	
Substance	3	Copper, [29H,31H-phthalocyaninato(2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	6.0	1.0	0.054054	mg	
Substance	3	2-Naphthalenecarboxylic acid, 4-[2-(5-chloro-4-methyl-2-sulfophenyl)diazenyl]-3-hydroxy-, calcium salt (1:1)	Supplier	7023-61-2	0.3	1.0	0.0027027	mg	
Substance	3	Silica	Supplier	7631-86-9	0.5	1.0	0.0045045	mg	
Substance	3	Glycerol	Supplier	56-81-5	0.05	1.0	4.5045E-4	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	3.0E-4	1.0	1.0E-5	mg	
Substance	3	Limestone	Supplier	1317-65-3	1.0	1.0	0.009009	mg	
Substance	3	Zeolites	Supplier	1318-02-1	1.0	1.0	0.009009	mg	
Substance	3	Aluminate (Al(OH)63-), (OC-6-11)-, magnesium carbonate hydroxide (2:6:1:4)	Supplier	11097-59-9	0.7	1.0	0.0063063	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	5.1357	1.0	0.04626752	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	0.009009	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.0050	1.0	4.5045E-5	mg	