



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	productcompliance	Contact Title			
Company Unique ID	TE Connectivity	Response Date	2019-09-18	Contact Email	productcompliance@te.com				
Contact Phone Number	18005226752								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1393217-1	Amount	8.745	Version	-	Identity			
Manufacturer Item Name	RE030005	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	RE030005 After Assembly				1.0	8.745	g	
Material	2	Iron Strip				1.0	4.57	g	
Substance	3	Vanadium	Supplier	7440-62-2	0.0070	1.0	3.199E-4	g	
Substance	3	Silicon	Supplier	7440-21-3	0.15	1.0	0.006855	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	4.5243E-4	g	
Substance	3	Titanium	Supplier	7440-32-6	0.0070	1.0	3.199E-4	g	
Substance	3	Manganese	Supplier	7439-96-5	0.36	1.0	0.016452	g	
Substance	3	Aluminum	Supplier	7429-90-5	0.09	1.0	0.004113	g	
Substance	3	Copper	Supplier	7440-50-8	0.08	1.0	0.003656	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.022	1.0	0.0010054	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	4.57E-4	g	
Substance	3	Carbon	Supplier	7440-44-0	0.01	1.0	4.57E-4	g	
Substance	3	Chromium	Supplier	7440-47-3	0.06	1.0	0.002742	g	
Substance	3	Iron	Supplier	7439-89-6	98.8887	1.0	4.51921359	g	
Substance	3	Sulfur	Supplier	7704-34-9	0.022	1.0	0.0010054	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.00457	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.57E-5	g	
Substance	3	Nitrogen	Supplier	7727-37-9	0.0070	1.0	3.199E-4	g	
Substance	3	Nickel	Nickel	7440-02-0	0.07	1.0	0.003199	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.285E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00456543	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.285E-4	g	
Material	2	Copper				1.0	1.512168	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.00151217	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	1.5122E-4	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.512168E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	1.512168E-5	g	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	1.50759369	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	1.5122E-4	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	3.0243E-4	g	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00151217	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	1.5122E-4	g	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	7.5608E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	7.56084E-6	g	
Material	2	Polyester Compound				1.0	0.617	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.0	1.0	0.11723	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	28.5	1.0	0.175845	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol]	Supplier	25971-63-5	34.2	1.0	0.211014	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	9.5	1.0	0.058615	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.8	1.0	0.054296	g	
Material	2	100-1777				1.0	0.42	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.1E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	1.0	1.0	0.0042	g	
Substance	3	Tin	Supplier	7440-31-5	1.2	1.0	0.00504	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.2E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	4.2E-5	g	
Substance	3	Titanium	Supplier	7440-32-6	0.8	1.0	0.00336	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	4.2E-5	g	
Substance	3	Copper	Supplier	7440-50-8	95.6685	1.0	0.4018077	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	4.2E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	4.2E-4	g	
Substance	3	Nickel	Nickel	7440-02-0	1.2	1.0	0.00504	g	
Material	2	PBT-GF45				1.0	0.154	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	11.0	1.0	0.01694	g	
Substance	3	Aromatic Brominated flame retardant - ISO 1043-4 code #FR(16)	Supplier	1043-4-FR16	8.0	1.0	0.01232	g	
Substance	3	Poly(butylene terephthalate) - ISO 1043-1 Term PBT	Supplier	1043-1-PBT	35.0	1.0	0.0539	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.00154	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	0.0693	g	
Material	2	Phos Bronze				1.0	0.05	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	5.0E-6	g	
Substance	3	Copper	Supplier	7440-50-8	91.9385	1.0	0.04596925	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	5.0E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	1.5E-4	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	1.0E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.0E-7	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	5.0E-5	g	
Substance	3	Tin	Supplier	7440-31-5	7.0	1.0	0.0035	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.75E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	7.5E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	5.0E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.5E-7	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.5E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	5.0E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.5E-5	g	
Material	2	Silver Alloy				1.0	0.05	g	
Substance	3	Aluminum	Supplier	7429-90-5	0.0010	1.0	5.0E-7	g	

Substance	3	Silver	Supplier	7440-22-4	99.783	1.0	0.0498915	g	
Substance	3	Bismuth	Supplier	7440-69-9	0.0010	1.0	5.0E-7	g	
Substance	3	Manganese	Supplier	7439-96-5	0.0010	1.0	5.0E-7	g	
Substance	3	Iron	Supplier	7439-89-6	0.0010	1.0	5.0E-7	g	
Substance	3	Copper	Supplier	7440-50-8	0.1	1.0	5.0E-5	g	
Substance	3	Silicon	Supplier	7440-21-3	0.0010	1.0	5.0E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0010	1.0	5.0E-7	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.11	1.0	5.5E-5	g	8(b) Cadmium and its compounds electrical contacts
Substance	3	Nickel	Nickel	7440-02-0	0.0010	1.0	5.0E-7	g	
Material	2	100-enamel				1.0	0.167832	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	100.0	1.0	0.167832	g	
Material	2	PBT-GF45				1.0	1.204	g	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2,2-[[1-(1-methylethylidene)bis(4,1-phenyleneoxy methylene)]bis[oxirane]	Supplier	25036-25-3	0.2131	1.0	0.00256572	g	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.2558	1.0	0.00307983	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	8.0173	1.0	0.09652829	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	42.6439	1.0	0.51343256	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0938	1.0	0.04928935	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	44.7761	1.0	0.53910424	g	