Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer
Company Unique ID	485203835	Response Date	2013-10-23	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	5-1462000-5	Amount	3690.78	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						
EUREACH-1212	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	CARRIER REGRIND				1.0	127.0	mg	
Material	2	Polyphenylene sulfide				1.0	127.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	40.0	1.0	50.8	mg	N/A
Substance	3	Poly(thio-1,4-phenylene)	Supplier	25212-74-2	60.0	1.0	76.2	mg	N/A
Sub-Item	1	MAGNETIC IRON PARTS 1				1.0	1177.0	mg	
Material	2	Ni Plating				1.0	1.50656	mg	
Substance	3	Nickel	Nickel	7440-02-0	100.0	1.0	1.50656	mg	N/A
Material	2	Special Steel				1.0	1175.49344	mg	
Substance	3	Iron	Supplier	7439-89-6	100.0	1.0	1175.49344	mg	N/A
Sub-Item	1	RESIN				1.0	27.8	mg	
Material	2	Epoxy				1.0	27.8	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2,2-[(1-methylethylidene)bis(4,1-phenyleneoxymethylene)]bis[oxirane]	Supplier	25036-25-3	100.0	1.0	27.8	mg	N/A
Sub-Item	1	MAGNETIC IRON PARTS 2				1.0	310.0	mg	
Material	2	Cu Plating				1.0	8.618	mg	
Substance	3	Copper	Supplier	7440-50-8	100.0	1.0	8.618	mg	N/A
Material	2	Special Steel				1.0	301.382	mg	
Substance	3	Iron	Supplier	7439-89-6	100.0	1.0	301.382	mg	N/A
Sub-Item	1	CONTACT PIECE				1.0	6.9	mg	
Material	2	Gold alloy				1.0	6.9	mg	
Substance	3	Nickel	Nickel	7440-02-0	18.4	1.0	1.2696	mg	N/A
Substance	3	Silver	Supplier	7440-22-4	50.8	1.0	3.5052	mg	N/A
Substance	3	Copper	Supplier	7440-50-8	25.4	1.0	1.7526	mg	N/A
Substance	3	Gold	Supplier	7440-57-5	5.4	1.0	0.3726	mg	N/A
Sub-Item	1	COIL BODY				1.0	194.0	mg	
Material	2	Polycarbonate				1.0	194.0	mg	
Substance	3	Polycarbonates	Supplier	25766-59-0	100.0	1.0	194.0	mg	N/A

Sub-Item	1	CONTACT SPRINGS				1.0	7.6	mg	
Material	2	Copper alloy				1.0	7.6	mg	
Substance	3	Copper	Supplier	7440-50-8	89.0	1.0	6.764	mg	N/A
Substance	3	Tin	Supplier	7440-31-5	2.0	1.0	0.152	mg	N/A
Substance	3	Nickel	Nickel	7440-02-0	9.0	1.0	0.684	mg	N/A
Sub-Item	1	RELAY HOUSING				1.0	487.0	mg	
Material	2	Polybuthylenet ereph-talate				1.0	487.0	mg	
Substance	3	1,4-Benzenedicarb oxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	74.0	1.0	360.38	mg	N/A
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	11.0	1.0	53.57	mg	N/A
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	15.0	1.0	73.05	mg	N/A
Sub-Item	1	ACTUATOR				1.0	24.0	mg	
Material	2	Polyoxymethyl ene, Polyacetal				1.0	24.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	10.0	1.0	2.4	mg	N/A
Substance	3	Poly(oxymethyl ene)	Supplier	9002-81-7	90.0	1.0	21.6	mg	N/A
Sub-Item	1	BASE TERMINALS				1.0	356.78	mg	
Material	2	Copper alloy				1.0	355.4028292	mg	
Substance	3	Copper	Supplier	7440-50-8	89.0	1.0	316.30852	mg	N/A
Substance	3	Tin	Supplier	7440-31-5	2.0	1.0	7.10806	mg	N/A
Substance	3	Nickel	Nickel	7440-02-0	9.0	1.0	31.98625	mg	N/A
Material	2	Cu Plating				1.0	0.0321102	mg	
Substance	3	Copper	Supplier	7440-50-8	100.0	1.0	0.0321102	mg	N/A
Material	2	Sn Plating				1.0	1.3450606	mg	
Substance	3	Tin	Supplier	7440-31-5	99.801	1.0	1.34238	mg	N/A
Substance	3	Chromium	Supplier	7440-47-3	0.099	1.0	0.00133161	mg	N/A
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00134506	mg	N/A
Sub-Item	1	MAGNETIC WIRE				1.0	972.7	mg	
Material	2	Polyurethane Plating				1.0	32.702174	mg	
Substance	3	Polyurethane - ISO 1043-1 Term PUR	Supplier	1043-1-PUR	100.0	1.0	32.70217	mg	N/A
Material	2	Cu100				1.0	939.997826	mg	
Substance	3	Copper	Supplier	7440-50-8	100.0	1.0	939.99783	mg	N/A