



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica John R	Contact Title	Sr Mgr Environmental Engineering																											
Company Unique ID	TE Connectivity	Response Date	2015-10-09	Contact Email	jrpenica@te.com																													
Contact Phone Number		7175923266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5-1622820-5	Amount	0.04441485	Version	-	Identity																												
Manufacturer Item Name	3520 5R6 5%	Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)																																	
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Resistive element				1.0	3.125E-4	g																										
Substance	2	Silver	Supplier	7440-22-4	35.0	1.0	1.0938E-4	g																										
Substance	2	Frits, chemicals	Supplier	65997-18-4	57.18	1.0	1.7869E-4	g																										
Substance	2	Ruthenium oxide (RuO2)	Supplier	12036-10-1	5.0	1.0	1.5625E-5	g																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	2.82	1.0	8.8125E-6	g	7(c)-I Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound																									
Material	1	Termination inner C3				1.0	1.339E-4	g																										
Substance	2	Nickel	Nickel	7440-02-0	80.0	1.0	1.0712E-4	g																										
Substance	2	Chromium	Supplier	7440-47-3	20.0	1.0	2.678E-5	g																										
Material	1	Substrate				1.0	0.04084681	g																										
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	100.0	1.0	0.04084681	g																										
Material	1	Marking				1.0	5.519E-5	g																										
Substance	2	Oxirane, 2,2-[(1-methylethylidene)bis(4,1-phenyleneoxy methylene)]bis-, homopolymer	Supplier	25085-99-8	52.63	1.0	2.90465E-5	g																										
Substance	2	Sulfuric acid, barium salt (1:1)	Supplier	7727-43-7	15.79	1.0	8.714501E-6	g																										
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	31.58	1.0	1.7429E-5	g																										
Material	1	Termination inner C1				1.0	2.367E-4	g																										
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	2.367E-4	g																										
Material	1	Termination inner C2				1.0	1.563E-4	g																										
Substance	2	Silver	Supplier	7440-22-4	95.0	1.0	1.4848E-4	g																										
Substance	2	Frits, chemicals	Supplier	65997-18-4	5.0	1.0	7.815E-6	g																										

Material	1	Protective coating G1				1.0	6.2781E-4	g	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	13.28	1.0	8.33725E-5	g	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	0.78	1.0	4.896879E-6	g	
Substance	2	Silicon oxide	Supplier	11126-22-0	28.13	1.0	1.766E-4	g	
Substance	2	Chromium oxide (Cr2O3)	Supplier	1308-38-9	4.69	1.0	2.944405E-5	g	
Substance	2	Bismuth oxide (Bi2O3)	Supplier	1304-76-3	53.12	1.0	3.3349E-4	g	
Material	1	Termination outer				1.0	4.6253E-4	g	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	4.6253E-4	g	
Material	1	Protective coating G2				1.0	0.0011132	g	
Substance	2	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2-(chloromethyl)oxirane	Supplier	25068-38-6	48.0	1.0	5.3433E-4	g	
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	5.34	1.0	5.944461E-5	g	
Substance	2	C.I. Pigment Black 28	Supplier	68186-91-4	13.33	1.0	1.4839E-4	g	
Substance	2	Silica, vitreous	Supplier	60676-86-0	33.33	1.0	3.7103E-4	g	
Material	1	Termination between				1.0	4.6992E-4	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	4.6992E-4	g	