Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A
Supplier Information							
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER
Company Unique ID	-	Response Date	2013-05-03	Contact Email	cc.wu@te.com		
Contact Phone Number	(86)21-33259321						
Legal Statement							
Supplier Acceptance	true						
Legal Statement							
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.							
Product							
Manufacturer Item number	1462033-5	Amount	2197.0	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requierement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	yoke regrind				1.0	495.8629	mg	
Substance	2	2-Naphthalenecarboxylic acid, 6-(acetyloxy)-, polymer with 4-(acetyloxy)benzoic acid	Supplier	70679-92-4	100.0	1.0	495.8629	mg	N/A
Material	1	carrier regrind				1.0	363.1641	mg	
Substance	2	2-Naphthalenecarboxylic acid, 6-(acetyloxy)-, polymer with 4-(acetyloxy)benzoic acid	Supplier	70679-92-4	100.0	1.0	363.1641	mg	N/A
Material	1	carrier terminals				1.0	5.0531	mg	
Substance	2	Miscellaneous	Supplier	system	2.0	1.0	0.10106	mg	N/A
Substance	2	Copper	Supplier	7440-50-8	89.0	1.0	4.49726	mg	N/A
Substance	2	Nickel	Nickel	7440-02-0	9.0	1.0	0.45478	mg	N/A
Material	1	Enamel varnish				1.0	3.0758	mg	
Substance	2	Polyurethane - ISO 1043-1 Term PUR	Supplier	1043-1-PUR	100.0	1.0	3.0758	mg	N/A
Material	1	permanent magnet				1.0	119.2971	mg	
Substance	2	Cobalt	Supplier	7440-48-4	7.87	1.0	9.38868	mg	N/A
Substance	2	Iron	Supplier	7439-89-6	83.75	1.0	99.91132	mg	N/A
Substance	2	Chromium	Supplier	7440-47-3	8.38	1.0	9.9971	mg	N/A
Material	1	housing regrind				1.0	162.1386	mg	
Substance	2	2-Naphthalenecarboxylic acid, 6-(acetyloxy)-, polymer with 4-(acetyloxy)benzoic acid	Supplier	70679-92-4	100.0	1.0	162.1386	mg	N/A
Material	1	coil terminals				1.0	25.4852	mg	
Substance	2	Miscellaneous	Supplier	system	2.0	1.0	0.5097	mg	N/A
Substance	2	Copper	Supplier	7440-50-8	89.0	1.0	22.68183	mg	N/A
Substance	2	Nickel	Nickel	7440-02-0	9.0	1.0	2.29367	mg	N/A
Material	1	armature				1.0	162.3583	mg	
Substance	2	Zinc	Supplier	7440-66-6	1.42	1.0	2.30549	mg	N/A
Substance	2	Tin	Supplier	7440-31-5	2.09	1.0	3.39329	mg	N/A
Substance	2	Copper	Supplier	7440-50-8	96.49	1.0	156.65952	mg	N/A
Material	1	fixed contacts				1.0	2.197	mg	

Substance	2	Silver	Supplier	7440-22-4	19.05	1.0	0.41853	mg	N/A
Substance	2	Copper	Supplier	7440-50-8	47.61	1.0	1.04599	mg	N/A
Substance	2	Gold	Supplier	7440-57-5	19.05	1.0	0.41853	mg	N/A
Substance	2	Nickel	Nickel	7440-02-0	14.29	1.0	0.31395	mg	N/A
Material	1	coil wire				1.0	299.8905	mg	
Substance	2	Copper	Supplier	7440-50-8	100.0	1.0	299.8905	mg	N/A
Material	1	change over spring				1.0	245.4049	mg	
Substance	2	Copper	Supplier	7440-50-8	69.06	1.0	169.47662	mg	N/A
Substance	2	Miscellaneous	Supplier	system	1.0	1.0	2.45405	mg	N/A
Substance	2	Nickel	Nickel	7440-02-0	29.94	1.0	73.47423	mg	N/A
Material	1	moveable contacts				1.0	2.197	mg	
Substance	2	Silver	Supplier	7440-22-4	19.05	1.0	0.41853	mg	N/A
Substance	2	Gold	Supplier	7440-57-5	19.05	1.0	0.41853	mg	N/A
Substance	2	Copper	Supplier	7440-50-8	47.61	1.0	1.04599	mg	N/A
Substance	2	Nickel	Nickel	7440-02-0	14.29	1.0	0.31395	mg	N/A
Material	1	resin				1.0	89.6376	mg	
Substance	2	Formaldehyde, polymer with 2-(chloromethyl)oxirane and 2-methylphenol	Supplier	29690-82-2	100.0	1.0	89.6376	mg	N/A
Material	1	armature regrind				1.0	19.773	mg	
Substance	2	2-Naphthalenecarboxylic acid, 6-(acetyloxy)-, polymer with 4-(acetyloxy)benzoic acid	Supplier	70679-92-4	100.0	1.0	19.773	mg	N/A
Material	1	yoke				1.0	201.4649	mg	
Substance	2	Zinc	Supplier	7440-66-6	1.15	1.0	2.31685	mg	N/A
Substance	2	Tin	Supplier	7440-31-5	2.28	1.0	4.5934	mg	N/A
Substance	2	Copper	Supplier	7440-50-8	96.57	1.0	194.55465	mg	N/A