Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance
Company Unique ID	TE Connectivity	Response Date	2015-04-03	Contact Email	jrpenica@te.com		
Contact Phone Number		717-592-3266					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	1623238-1	Amount	4.74171	Version	-	Identity	
Manufacturer Item Name	CRG0805 1% 4K3	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)						
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Termination between				1.0	0.15019	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.15019	mg	
Material	1	Protective coating G2				1.0	0.069624	mg	
Substance	2	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2-(chloromethyl)oxirane	Supplier	25068-38-6	48.0	1.0	0.03341952	mg	
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	5.34	1.0	0.00371792	mg	
Substance	2	C.I. Pigment Black 28	Supplier	68186-91-4	13.33	1.0	0.00928088	mg	
Substance	2	Silica, vitreous	Supplier	60676-86-0	33.33	1.0	0.02320568	mg	
Material	1	Termination inner C3				1.0	0.0258	mg	
Substance	2	Nickel	Nickel	7440-02-0	80.0	1.0	0.02064	mg	
Substance	2	Chromium	Supplier	7440-47-3	20.0	1.0	0.00516	mg	
Material	1	Termination outer				1.0	0.14783	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.14783	mg	
Material	1	Termination inner C1				1.0	0.059025	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	0.059025	mg	
Material	1	Marking				1.0	0.00436	mg	
Substance	2	Oxirane, 2,2-[(1-methylethylidene)bis(4,1-phenyleneoxymethylene)]bis-, homopolymer	Supplier	25085-99-8	52.63	1.0	0.00229467	mg	
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	31.58	1.0	0.00137689	mg	
Substance	2	Sulfuric acid, barium salt (1:1)	Supplier	7727-43-7	15.79	1.0	6.8844E-4	mg	
Material	1	Resistive element				1.0	0.027	mg	
Substance	2	Frits, chemicals	Supplier	65997-18-4	57.29	1.0	0.0154683	mg	
Substance	2	Silver	Supplier	7440-22-4	35.0	1.0	0.00945	mg	
Substance	2	Ruthenium oxide (RuO2)	Supplier	12036-10-1	5.0	1.0	0.00135	mg	

Substance	2	Lead	Lead/Lead Compounds	7439-92-1	2.71	1.0	7.317E-4	mg	7(c)-I Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound
Material	1	Substrate				1.0	4.179636	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	100.0	1.0	4.17964	mg	
Material	1	Termination inner C2				1.0	0.038975	mg	
Substance	2	Silver	Supplier	7440-22-4	95.0	1.0	0.03702625	mg	
Substance	2	Frits, chemicals	Supplier	65997-18-4	5.0	1.0	0.00194875	mg	
Material	1	Protective coating G1				1.0	0.03927	mg	
Substance	2	Bismuth oxide (Bi2O3)	Supplier	1304-76-3	53.12	1.0	0.02086022	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	0.78	1.0	3.0631E-4	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	13.28	1.0	0.00521506	mg	
Substance	2	Silicon oxide	Supplier	11126-22-0	28.13	1.0	0.01104665	mg	
Substance	2	Chromium oxide (Cr2O3)	Supplier	1308-38-9	4.69	1.0	0.00184176	mg	