Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND
Company Unique ID	TE Connectivity	Response Date	2018-04-17	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	167294-1	Amount	9349.561845	Version	-	Identity	
Manufacturer Item Name	25P HDP20 PLUG ASSY	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	C42334A 383C237=MT. BOVENDEEL				1.0	3190.0	mg	
Material	2	DC 04				1.0	3000.0036	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.015	1.0	0.45	mg	N/A
Substance	3	Carbon	Supplier	7440-44-0	0.04	1.0	1.2	mg	N/A
Substance	3	Iron	Supplier	7439-89-6	99.73	1.0	2991.90359	mg	N/A
Substance	3	Manganese	Supplier	7439-96-5	0.2	1.0	6.00001	mg	N/A
Substance	3	Phosphorus	Supplier	7723-14-0	0.015	1.0	0.45	mg	N/A
Material	2	Ni Plating				1.0	60.0039	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.4	1.0	0.24002	mg	N/A
Substance	3	Sulfur	Supplier	7704-34-9	0.015	1.0	0.00900059	mg	N/A
Substance	3	Nickel	Nickel	7440-02-0	99.585	1.0	59.75488	mg	N/A
Material	2	Sn Plating				1.0	129.9925	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.0259985	mg	N/A
Substance	3	Carbon	Supplier	7440-44-0	0.505	1.0	0.65646	mg	N/A
Substance	3	Tin	Supplier	7440-31-5	99.46	1.0	129.29054	mg	N/A
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.015	1.0	0.01949888	mg	N/A
Sub-Item	1	25P.REAR PLG.INSERT				1.0	1936.6	mg	
Material	2	PBT-GF15				1.0	1936.6	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	29.049	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	9.683	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	7.7464	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	55.9	1.0	1082.5594	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	96.83	mg	

Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	3.0	1.0	58.098	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	17.4294	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[(1-oxooctadecyl)oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	9.683	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	329.222	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	5.8098	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	15.0	1.0	290.49	mg	
Sub-Item	1	25P.FR.INSERT,PLUG				1.0	1939.1	mg	
Material	2	PBT-GF15				1.0	1939.1	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	29.0865	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	9.6955	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	7.7564	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	55.9	1.0	1083.9569	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	96.955	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	3.0	1.0	58.173	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	17.4519	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[(1-oxooctadecyl)oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	9.6955	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	329.647	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	5.8173	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	15.0	1.0	290.865	mg	
Sub-Item	1	25P.HDP20 REAR SH.				1.0	2283.861845	mg	
Material	2	Tin Plate				1.0	75.943725	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.05316061	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.15189	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	75.73868	mg	
Material	2	Carbon Steel				1.0	2183.2	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.21832	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.21832	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.01	1.0	0.21832	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.1832	mg	
Substance	3	Iron	Supplier	7439-89-6	99.7075	1.0	2176.81414	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.021832	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.021832	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.010916	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.0916	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.1832	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.21832	mg	
Material	2	Nickel Plate				1.0	24.71812	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.04943624	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.02471812	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	24.64397	mg	