Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	John R. Penica	**Contact Title**	Mgr. Global Product Compliance
Company Unique ID	TE Connectivity	**Response Date**	2015-08-24	**Contact Email**	jrpenica@te.com		
Contact Phone Number		717-592-3266					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	1676378-2	**Amount**	4.7072605	**Version**	-	**Identity**	
Manufacturer Item Name	RN 0805 56R2 0.1% 10PPM 1KRL	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Upside Electrode				1.0	0.05379975	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.01075995	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	0.00537998	mg	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	0.00806996	mg	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.02958986	mg	
Material	1	Overcoat				1.0	0.04332563	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	12.0	1.0	0.00519908	mg	
Substance	2	Carbon black	Supplier	1333-86-4	3.0	1.0	0.00129977	mg	
Substance	2	Resin acids and Rosin acids	Supplier	73138-82-6	35.0	1.0	0.01516397	mg	
Substance	2	Acetamide	Supplier	60-35-5	20.0	1.0	0.00866512	mg	
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	10.0	1.0	0.00433256	mg	
Substance	2	Silica, vitreous	Supplier	60676-86-0	20.0	1.0	0.00866512	mg	
Material	1	Resistor Layer				1.0	1.750159E-5	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	1.750159E-5	mg	
Material	1	Edge Electrode				1.0	2.299967E-5	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	2.299967E-5	mg	
Material	1	Substrate				1.0	4.49003926	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	96.0	1.0	4.31044	mg	
Substance	2	Quartz (SiO2)	Supplier	14808-60-7	3.0	1.0	0.1347	mg	
Substance	2	Magnesium oxide (MgO)	Supplier	1309-48-4	1.0	1.0	0.04490039	mg	
Material	1	Backside Electrode				1.0	0.05379975	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.01075995	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	0.00537998	mg	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	0.00806996	mg	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.02958986	mg	
Material	1	Tin Plating				1.0	0.02981579	mg	

Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.02981579	mg	
Material	1	Marking				1.0	0.02372883	mg	
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	20.0	1.0	0.00474577	mg	
Substance	2	Cellulose, ethyl ether	Supplier	9004-57-3	80.0	1.0	0.01898306	mg	
Material	1	Nickel Plating				1.0	0.012711	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.012711	mg	