Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance
Company Unique ID	TE Connectivity	Response Date	2015-01-09	Contact Email	jrpenica@te.com		
Contact Phone Number		717-592-3266					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	6-1879337-6	Amount	1.832	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Substrate				1.0	1.75	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	96.0	1.0	1.68	mg	
Substance	2	Magnesium oxide (MgO)	Supplier	1309-48-4	1.0	1.0	0.0175	mg	
Substance	2	Quartz (SiO2)	Supplier	14808-60-7	3.0	1.0	0.0525	mg	
Material	1	Upside Electrode				1.0	0.021	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.0042	mg	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	0.00315	mg	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.01155	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	0.0021	mg	
Material	1	Nickel Plating				1.0	0.00515	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.00515	mg	
Material	1	Backside Electrode				1.0	0.021	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	0.0021	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.0042	mg	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.01155	mg	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	0.00315	mg	
Material	1	Marking				1.0	0.01	mg	
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	20.0	1.0	0.0020	mg	
Substance	2	Cellulose, ethyl ether	Supplier	9004-57-3	80.0	1.0	0.0080	mg	
Material	1	Tin Plating				1.0	0.00945	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.00945	mg	
Material	1	Overcoat				1.0	0.0154	mg	
Substance	2	Silica, vitreous	Supplier	60676-86-0	20.0	1.0	0.00308	mg	
Substance	2	Resin acids and Rosin acids	Supplier	73138-82-6	35.0	1.0	0.00539	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	12.0	1.0	0.001848	mg	
Substance	2	Carbon black	Supplier	1333-86-4	3.0	1.0	4.62E-4	mg	
Substance	2	Acetamide	Supplier	60-35-5	20.0	1.0	0.00308	mg	
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	10.0	1.0	0.00154	mg	