



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	485203835	Response Date	2014-02-19	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1825955-2	Amount	275.9999995	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	STEMBL - 7				1.0	65.67696	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	16.82	1.0	11.04686	mg	
Substance	2	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	83.18	1.0	54.6301	mg	
Material	1	TERMINAL Plating - 3				1.0	0.23924469	mg	
Substance	2	Silver	Supplier	7440-22-4	53.98	1.0	0.12914	mg	
Substance	2	Nickel	Nickel	7440-02-0	46.02	1.0	0.1101	mg	
Material	1	CASE - 1				1.0	95.22	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	20.28	1.0	19.31062	mg	
Substance	2	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	79.72	1.0	75.90938	mg	
Material	1	DOVE CONTACT - 4				1.0	19.32	mg	
Substance	2	Copper	Supplier	7440-50-8	90.8	1.0	17.54256	mg	
Substance	2	Tin	Supplier	7440-31-5	9.0	1.0	1.7388	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.2	1.0	0.03864	mg	
Material	1	TERMINAL - 2				1.0	63.24627531	mg	
Substance	2	Copper	Supplier	7440-50-8	70.58	1.0	44.63922	mg	
Substance	2	Zinc	Supplier	7440-66-6	29.42	1.0	18.60705	mg	
Material	1	DOVE CONTACT plating - 5				1.0	0.55476	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	0.55476	mg	
Material	1	Cover plating				1.0	0.0634855	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.0634855	mg	
Material	1	COVER - 6				1.0	31.679274	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.00633585	mg	
Substance	2	Carbon	Supplier	7440-44-0	0.11	1.0	0.0348472	mg	
Substance	2	Molybdenum	Supplier	7439-98-7	0.04	1.0	0.01267171	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.53	1.0	0.1679	mg	
Substance	2	Copper	Supplier	7440-50-8	0.18	1.0	0.05702269	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.02	1.0	0.00633585	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.04	1.0	0.01267171	mg	
Substance	2	Iron	Supplier	7439-89-6	98.84	1.0	31.31179	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.09	1.0	0.02851135	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.13	1.0	0.04118306	mg	