Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Benfer David W	**Contact Title**	Product Compliance Engineer for DND
Company Unique ID	TE Connectivity	**Response Date**	2018-04-04	**Contact Email**	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	6-5530843-5	**Amount**	14245.72990551	**Version**	-	**Identity**	
Manufacturer Item Name	CONN SEC II 31 POS 100C/L	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	STD EDGE II STRP PLTD 100CL				31.0	73.47460321	mg	
Material	2	Tin Plate				31.0	0.215	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	31.0	4.3E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	31.0	0.21442	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	31.0	1.505E-4	mg	
Material	2	Gold Plate				31.0	0.00860321	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	31.0	0.0085774	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	31.0	2.580963E-5	mg	
Material	2	Phos Bronze				31.0	72.5	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	31.0	68.65641	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	31.0	0.0145	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	31.0	0.00725	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	31.0	3.2625	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	31.0	0.003625	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	31.0	0.0725	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	31.0	0.00725	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	31.0	7.25E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	31.0	0.2175	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	31.0	0.0725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	31.0	0.0725	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	31.0	0.003625	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	31.0	0.03625	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	31.0	0.0725	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	31.0	3.625E-4	mg	
Material	2	Nickel Plate				31.0	0.751	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	31.0	7.51E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	31.0	0.001502	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	31.0	0.74875	mg	
Sub-Item	1	STD EDGE II HSG 31 POS 100C/L				1.0	9690.0	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	9690.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	48.45	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	3391.5	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	19.38	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	19.38	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	290.7	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	193.8	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	96.9	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	48.45	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	96.9	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	3546.54	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	48.45	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	1744.2	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	48.45	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	96.9	mg	
Sub-Item	1	CONTACT, STD EDGE II, .100 CL				31.0	73.484426	mg	
Material	2	Tin Plate				31.0	0.215326	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	31.0	4.3065E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	31.0	0.21474	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	31.0	1.5073E-4	mg	
Material	2	Gold Plate				31.0	0.0172	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	31.0	0.0171484	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	31.0	5.16E-5	mg	
Material	2	Phos Bronze				31.0	72.5	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	31.0	68.65641	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	31.0	0.0145	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	31.0	0.00725	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	31.0	3.2625	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	31.0	0.003625	mg	

Substance	3	Iron	Supplier	7439-89-6	0.1	31.0	0.0725	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	31.0	0.00725	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	31.0	7.25E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	31.0	0.2175	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	31.0	0.0725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	31.0	0.0725	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	31.0	0.003625	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	31.0	0.03625	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	31.0	0.0725	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	31.0	3.625E-4	mg	
Material	2	Nickel Plate				31.0	0.7519	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	31.0	7.519E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	31.0	0.0015038	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	31.0	0.74964	mg	