



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2017-01-10	Contact Email	cc.wu@te.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	2-644803-4	Amount	745.18	Version	-	Identity																												
Manufacturer Item Name	04P MTA100 SHRD HDR ASSY RA FL	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	04P MTA100 SHRD HDR HSG				1.0	519.5	mg																										
Material	2	PBT-GF15 FR(17)				1.0	519.5	mg																										
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	5.195	mg																										
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	57.0	1.0	296.115	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	88.315	mg																										
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	15.0	1.0	77.925	mg																										
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	10.0	1.0	51.95	mg																										
Sub-Item	1	MTA100 BANDO/PIN ASSY .625 LF				4.0	56.42	mg																										
Material	2	Phos Bronze				4.0	54.469	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	5.4469E-4	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	4.0	0.00817035	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.0108938	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	4.0	0.19064	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.0054469	mg																										
Substance	3	Tin	Supplier	7440-31-5	5.8	4.0	3.1592	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.054469	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	0.16341	mg																										
Substance	3	Copper	Supplier	7440-50-8	93.1335	4.0	50.72889	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	0.0054469	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	0.054469	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	0.054469	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	4.0	0.0054469	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	2.7235E-4	mg																										

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.0272345	mg	
Material	2	Nickel Plate				4.0	0.456	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	9.12E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	4.56E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.45463	mg	
Material	2	Tin Plate				4.0	1.495	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	4.0	1.49096	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	0.00299	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	4.0	0.0010465	mg	