Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A
Supplier Information							
Company Name	TE Connectivity	Request Document ID		Contact Name	Vincent M Pascucci	Contact Title	Compliance Engineer
Company Unique ID	-	Response Date	2013-02-26	Contact Email	vincent.pascucci@te.com		
Contact Phone Number		717-986-7822					
Legal Statement							
Supplier Acceptance	true						
Legal Statement							
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.							
Product							
Manufacturer Item number	641217-6	Amount	5245.8120204	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions						
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products						
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	640530-6				1.0	1318.8	mg	
Material	2	PA66				1.0	1292.424	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	99.0	1.0	1279.49976	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	12.92424	mg	
Material	2	COLORANT				1.0	26.376	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	14.76	1.0	3.8931	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	1.0	0.26376	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediyl)]	Supplier	25038-54-4	84.24	1.0	22.21914	mg	
Sub-Item	1	641138-2				6.0	654.5020034	mg	
Material	2	Gold Plate				6.0	0.9	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	6.0	0.891	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	6.0	0.0090	mg	
Material	2	Phos Bronze				6.0	649.4	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	6.0	614.87465	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	6.0	0.12988	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	6.0	0.06494	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	6.0	29.223	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	6.0	0.09741	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.06494	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	6.0	0.6494	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.006494	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	6.0	1.9482	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	6.0	0.6494	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.6494	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.06494	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.3247	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	6.0	0.6494	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.003247	mg	
Material	2	Tin-Lead Plate				6.0	1.7420034	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	6.0	0.12194	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	6.0	1.60787	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	6.0	0.01219402	mg	
Material	2	Nickel Plate				6.0	2.46	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	6.0	0.00492	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.00246	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	2.45262	mg	