Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer for DND
Company Unique ID	TE Connectivity	Response Date	2017-12-18	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	2-84534-1	Amount	1545.346596	Version	-	Identity	
Manufacturer Item Name	1.25MM FFC POST PLATED V 21P	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1.25MM FFC CONTACT V RE-REELED				11.0	34.464236	mg	
Material	2	Nickel Plate				11.0	0.304236	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	11.0	6.0847E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	11.0	3.0424E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	11.0	0.30332	mg	
Material	2	Tin Plate				11.0	0.16	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	11.0	1.12E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	11.0	3.2E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	11.0	0.15957	mg	
Material	2	Phos Bronze				11.0	34.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	11.0	32.19749	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	11.0	0.0068	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	11.0	0.0034	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	11.0	1.53	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	11.0	0.0017	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	11.0	0.034	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	11.0	0.0034	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	11.0	3.4E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	11.0	0.102	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	11.0	0.034	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	11.0	0.034	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	11.0	0.0017	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	11.0	0.017	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	11.0	0.034	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	11.0	1.7E-4	mg	

Sub-Item	1	1.25MM FFC CONTACT H RE-REELED				10.0	23.864	mg	
Material	2	Nickel Plate				10.0	0.24	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	4.8E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	2.4E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.23928	mg	
Material	2	Tin Plate				10.0	0.124	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	10.0	8.68E-5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	2.48E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	10.0	0.12367	mg	
Material	2	Phos Bronze				10.0	23.5	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	10.0	22.25415	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.0047	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.00235	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	10.0	1.0575	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	10.0	0.001175	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.0235	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.00235	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	2.35E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.0705	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	10.0	0.0235	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.0235	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	10.0	0.001175	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.01175	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.0235	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	1.175E-4	mg	
Sub-Item	1	1.25MM FFC HSG 21P NATURAL				1.0	927.6	mg	
Material	2	PBT-GF30				1.0	927.6	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.5	1.0	32.466	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylidene)bis[(2,6-dibromo-4,1-phenylene)oxymethylene]]bis[oxirane]	Supplier	68928-70-1	12.0	1.0	111.312	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	54.5	1.0	505.542	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	278.28	mg	