Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china
Company Unique ID	TE Connectivity	Response Date	2018-06-08	Contact Email	cc.wu@te.com		
Contact Phone Number		86-2124071672					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	770024-1	Amount	4360.0	Version	-	Identity	
Manufacturer Item Name	02P UMNLII IN-LINE CAP HSG KIT	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	02P UMNL II CAP-FRONT 94VO				1.0	2860.0	mg	
Material	2	PA				1.0	2860.0	mg	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	9.32932	mg	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	13.26182	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	0.00858	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	0.9451	1.0	27.02986	mg	
Substance	3	Benzenepropanamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	11.45144	mg	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	0.09438	mg	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	0.715	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	5.75432	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.1901	1.0	5.43686	mg	
Substance	3	1,3,5-Triazine-2,4,6(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	259.45062	mg	

Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	2527.4678	mg	
Sub-Item	1	02P UMNL II CAP REAR 94VO				1.0	1500.0	mg	
Material	2	PA				1.0	1500.0	mg	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	4.893	mg	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	6.9555	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	0.0045	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	0.9451	1.0	14.1765	mg	
Substance	3	Benzenepropanamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	6.006	mg	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	0.0495	mg	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	0.375	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	3.018	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.1901	1.0	2.8515	mg	
Substance	3	1,3,5-Triazine-2,4,6(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	136.0755	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	1325.595	mg	