Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Wu, Cc	**Contact Title**	Engineer Product Compliance china
Company Unique ID	485203835	**Response Date**	2013-12-08	**Contact Email**	cc.wu@tycoelectronics.com		
Contact Phone Number		86-2124071672					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	770247-4	**Amount**	645.087	**Version**	-	**Identity**	
Manufacturer Item Name		**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true						
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	770004-4				1.0	645.087	mg	
Material	2	Tin-Lead Plate				1.0	4.453	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	1.0	0.031171	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	1.0	4.11012	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	1.0	0.31171	mg	
Material	2	Phos Bronze				1.0	634.385	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	600.65792	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.12688	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.0634385	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	28.54733	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.09515775	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.63439	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0634385	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00634385	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	1.90316	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.63439	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.63439	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0634385	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.31719	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.63439	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00317192	mg	
Material	2	Gold Plate				1.0	0.623	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.001869	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.62113	mg	
Material	2	Nickel Plate				1.0	5.626	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.011252	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.005626	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	5.60912	mg	