Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer for DND
Company Unique ID	TE Connectivity	Response Date	2015-10-15	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	292174-7	Amount	624.225601	Version	-	Identity	
Manufacturer Item Name	CT BOX HDR V SMT 7P O/TAPE NAT	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	CT BOX HDR V SMT 7P ASSY NAT W				1.0	624.225601	mg	
Material	2	Nickel Plate				1.0	3.186959	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00637392	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00318696	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	3.1774	mg	
Material	2	PPA-GF30				1.0	391.0	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0020	1.0	0.00782	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	7.82	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	2.0	1.0	7.82	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	23.9959	1.0	93.82397	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	44.3	1.0	173.213	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.7	1.0	2.737	mg	
Substance	3	Magnesium oxide (MgO)	Supplier	1309-48-4	6.0	1.0	23.46	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	21.0	1.0	82.11	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	1.0E-4	1.0	3.91E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0020	1.0	0.00782	mg	
Material	2	Brass				1.0	48.4	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	4.84E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	13.56289	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.0242	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00484	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.0242	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0484	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	34.606	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.84E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00484	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.42E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.0968	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00242	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0242	mg	
Material	2	Tin Plate				1.0	1.32	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	1.31644	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00264	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	9.24E-4	mg	
Material	2	Brass				1.0	177.786147	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.35557	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.01777861	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.4675	1.0	63.0563	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.17779	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00177786	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.08889307	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.08889307	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	1.0	113.78313	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00177786	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.01777861	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.17779	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	8.8893E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.01777861	mg	
Material	2	Tin Plate				1.0	2.532495	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00506499	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	2.52566	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.00177275	mg	