Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A
Supplier Information							
Company Name	TE Connectivity	Request Document ID		Contact Name	Vincent M Pascucci	Contact Title	Compliance Engineer
Company Unique ID	-	Response Date	2013-02-26	Contact Email	vincent.pascucci@te.com		
Contact Phone Number		717-986-7822					
Legal Statement							
Supplier Acceptance	true						
Legal Statement							
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.							
Product							
Manufacturer Item number	8-34823-2	Amount	1920.954	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requierement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	27012-2				1.0	400.0	mg	
Material	2	Colorant				1.0	8.36	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	4.4	1.0	0.36784	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	1.0E-4	1.0	1.0E-5	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	0.0836	mg	
Substance	3	Ethene, homopolymer, oxidized	Supplier	68441-17-8	2.0	1.0	0.1672	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 4,4-dibutyl-10-ethyl-7-oxo-, 2-ethylhexyl ester	Supplier	10584-98-2	2.0	1.0	0.1672	mg	
Substance	3	Benzenesulfonic acid, 4-[[1-[[(2-chlorophenyl)amino]carbonyl]-2-oxop...	Supplier	71832-85-4	9.0	1.0	0.7524	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	22.0	1.0	1.8392	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.5	1.0	0.0418	mg	
Substance	3	Aluminum oxide (Al2O3)	Supplier	1344-28-1	0.5	1.0	0.0418	mg	
Substance	3	Limestone	Supplier	1317-65-3	1.5	1.0	0.1254	mg	
Substance	3	Stannane, butyltrichloro-	Supplier	1118-46-3	0.1	1.0	0.00836	mg	
Substance	3	Aluminate (Al(OH)63-), (OC-6-11)-, magnesium carbonate hydroxide (2:6:1:4)	Supplier	11097-59-9	1.0	1.0	0.0836	mg	
Substance	3	Ethene, chloro-, homopolymer	Polyvinyl Chloride (PVC)	9002-86-2	55.9999	1.0	4.68159	mg	
Material	2	PVC				1.0	391.64	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	2.0E-4	1.0	7.8328E-4	mg	
Substance	3	Limestone	Supplier	1317-65-3	2.0	1.0	7.8328	mg	

Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	1.5	1.0	5.8746	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.1	1.0	0.39164	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	8.3998	1.0	32.89698	mg	
Substance	3	Ethene, chloro-, homopolymer	Polyvinyl Chloride (PVC)	9002-86-2	88.0	1.0	344.6432	mg	
Sub-Item	1	33718				1.0	1520.954	mg	
Material	2	Tin Plate				1.0	8.685	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	8.64157	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.03474	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.008685	mg	
Material	2	Copper				1.0	1512.269	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.75613	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.51227	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.01512269	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	1507.69439	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01512269	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.15123	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.15123	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.30245	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.51227	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00756134	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.15123	mg	