Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Rohde, Daniel F.	Contact Title	Prod Sustaining Engineer
Company Unique ID	TE Connectivity	Response Date	2015-05-02	Contact Email	daniel.rohde@te.com		
Contact Phone Number		+1-717-986-3211					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	8-51864-1	Amount	1028.463587	Version	-	Identity	
Manufacturer Item Name	TERMINAL,PID G R IR 14 6	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	BODY,RING 14 6				1.0	628.982187	mg	
Material	2	Tin Plate				1.0	6.657187	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	6.6239	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.02662875	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00665719	mg	
Material	2	Copper				1.0	622.325	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.31116	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.62232	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00622325	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	620.44247	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00622325	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0622325	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0622325	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.12446	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.62232	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00311163	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0622325	mg	
Sub-Item	1	SLEEVE ASSEMBLY 14 IR				1.0	399.4814	mg	
Material	2	PA66				1.0	103.744476	mg	
Substance	3	Copper	Supplier	7440-50-8	0.02	1.0	0.0207489	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.1	1.0	1.14119	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	98.78	1.0	102.47879	mg	
Substance	3	Bromine	Supplier	7726-95-6	0.1	1.0	0.10374	mg	
Material	2	COLORANT				1.0	1.047924	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.32	1.0	0.00335336	mg	

Substance	3	3H-Naphtho[1,2,3-de]quinoline-2,7-dione, 3-methyl-6-[(4-methylphenyl)amino]-	Supplier	81-39-0	0.1	1.0	0.00104792	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.0090	1.0	9.431316E-5	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	98.98	1.0	1.03724	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.0010	1.0	1.047924E-5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.17	1.0	0.00178147	mg	
Substance	3	Copper, [29H,31H-phthalocyaninato(2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	0.42	1.0	0.00440128	mg	
Material	2	Tin Plate				1.0	7.045	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	7.00978	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.02818	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.007045	mg	
Material	2	Copper				1.0	287.644	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.14382	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.28764	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00287644	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	286.77388	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00287644	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0287644	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0287644	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0575288	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.28764	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00143822	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0287644	mg	