Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	John R Penica	**Contact Title**	Sr Mgr Environmental Engineering
Company Unique ID	TE Connectivity	**Response Date**	2016-10-13	**Contact Email**	jrpenica@te.com		
Contact Phone Number		+1-717-592-3266					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	3-1676480-9	**Amount**	5.3266E-4	**Version**	-	**Identity**	
Manufacturer Item Name	CRG0402 1% 270K	**Weight Uom**	g	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)						
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Resistive element				1.0	3.2E-6	g	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	3.0	1.0	9.6E-8	g	7(c)-I Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound
Substance	2	Frits, chemicals	Supplier	65997-18-4	57.0	1.0	1.824E-6	g	
Substance	2	Silver	Supplier	7440-22-4	35.0	1.0	1.12E-6	g	
Substance	2	Ruthenium oxide (RuO2)	Supplier	12036-10-1	5.0	1.0	1.6E-7	g	
Material	1	Substrate				1.0	4.3149E-4	g	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	100.0	1.0	4.3149E-4	g	
Material	1	Termination inner C3				1.0	7.0E-8	g	
Substance	2	Nickel	Nickel	7440-02-0	80.0	1.0	5.6E-8	g	
Substance	2	Chromium	Supplier	7440-47-3	20.0	1.0	1.4E-8	g	
Material	1	Termination outer				1.0	3.504E-5	g	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	3.504E-5	g	
Material	1	Protective coating G2				1.0	5.84E-6	g	
Substance	2	Phenol, 4,4-(1-methylethylidene)bis-, polymer with 2-(chloromethyl)oxirane	Supplier	25068-38-6	48.0	1.0	2.8032E-6	g	
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	5.34	1.0	3.11856E-7	g	
Substance	2	C.I. Pigment Black 28	Supplier	68186-91-4	13.33	1.0	7.78472E-7	g	
Substance	2	Silica, vitreous	Supplier	60676-86-0	33.33	1.0	1.946472E-6	g	

Material	1	Termination between				1.0	3.56E-5	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	3.56E-5	g	
Material	1	Termination inner C2				1.0	6.63E-6	g	
Substance	2	Silver	Supplier	7440-22-4	95.0	1.0	6.2985E-6	g	
Substance	2	Frits, chemicals	Supplier	65997-18-4	5.0	1.0	3.315E-7	g	
Material	1	Protective coating G1				1.0	3.02E-6	g	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	13.28	1.0	4.01056E-7	g	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	0.78	1.0	2.3556E-8	g	
Substance	2	Silicon oxide	Supplier	11126-22-0	28.13	1.0	8.49526E-7	g	
Substance	2	Chromium oxide (Cr2O3)	Supplier	1308-38-9	4.69	1.0	1.41638E-7	g	
Substance	2	Bismuth oxide (Bi2O3)	Supplier	1304-76-3	53.12	1.0	1.604224E-6	g	
Material	1	Termination inner C1				1.0	1.177E-5	g	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	1.177E-5	g	