Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china
Company Unique ID	TE Connectivity	Response Date	2016-05-24	Contact Email	cc.wu@te.com		
Contact Phone Number		86-2124071672					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	3-644284-3	Amount	2734.8067	Version	-	Identity	
Manufacturer Item Name	03P MTA156 ASSY 18AWG ORA LF	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	03P MTA156 HSG ORNG CE W/LR				1.0	769.3	mg	
Material	2	COLORANT				1.0	15.386	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediyl)]	Supplier	25038-54-4	96.85	1.0	14.90134	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.15	1.0	0.48466	mg	
Material	2	PA66				1.0	753.914	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	99.355	1.0	749.05125	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.0020	1.0	0.01507828	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.3	1.0	2.26174	mg	
Substance	3	Water	Supplier	7732-18-5	0.2	1.0	1.50783	mg	
Substance	3	Aluminum, hydroxybis(octadecanoato-.kappa.O)-	Supplier	300-92-5	0.14	1.0	1.05548	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0030	1.0	0.02261742	mg	
Sub-Item	1	MTA156 CONT 18AWG AUNI/PHBZ				3.0	655.1689	mg	
Material	2	Nickel Plate				3.0	3.1913	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.0063826	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	0.0031913	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	3.18173	mg	
Material	2	Phos Bronze				3.0	649.4	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	3.0	614.97206	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	3.0	0.12988	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	3.0	0.06494	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	3.0	29.223	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	3.0	0.03247	mg	

Substance	3	Iron	Supplier	7439-89-6	0.1	3.0	0.6494	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.06494	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	0.006494	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	3.0	1.9482	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	3.0	0.6494	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.6494	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.03247	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.3247	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	3.0	0.6494	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	0.003247	mg	
Material	2	Tin Plate				3.0	1.6776	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.0033552	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	1.67307	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	0.00117432	mg	
Material	2	Gold Plate				3.0	0.9	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	3.0	0.891	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	3.0	0.0090	mg	