

REV. 4 1/10/96

COIL:


RESISTANCE	310 OHMS ± 10%
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	6.0 VDC
MUST RELEASE	3.0 VDC MAX, 0.6 VDC MIN.

ENVIRONMENT:

VIBRATION	10	CPS TO	2000	CPS @	20	g's
SHOCK	100	g's	6	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES: OPERATE & RELEASE 4 MS MAX.
CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
1 AMP 28 VDC RESISTIVE
100,000 OPERATIONS

DR. R.B. 1/18/91 CK. 1/10/96



CUST. QPL
CUST. NO. M39016/34-005

TYPE 'MFW' RELAY

MFW1201S07