

4




3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE CONNECTIVITY IRELAND LTD, ISC, BLOCK 1, UNIVERSITY OF LIMERICK (NTP), CASTLETROY, LIMERICK, IRELAND

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		ORIGINAL ISSUE	09/14	JM	-



DETAIL A
SCALE 2:1

No SHEDS	CREEPAGE LENGTH	FLASHOVER DISTANCE
5	404	172

NOTE	
HOUSING PRINT	 Bowthorpe EMP Surge Arrester Is 21kA / In 10kA 50/60 Hz STD STUD LENGTH 45±2mm. OTHER LENGTHS AVAILABLE DEPENDING ON ACCESSORY SELECTION

REFER TO TECHNICAL DATASHEETS FOR ALL OTHER PRODUCT DETAILS

PRODUCT	TEXT A	TEXT B	TEXT C	TEXT D
DA1-04B	DA1-04B	LOT No	Uc 3.2kV	Ur 4kV
DA1-06B	DA1-06B	LOT No	Uc 4.8kV	Ur 6kV
DA1-08B	DA1-08B	LOT No	Uc 6.4kV	Ur 8kV
DA1-10B	DA1-10B	LOT No	Uc 8kV	Ur 10kV
DA1-12B	DA1-12B	LOT No	Uc 9.6kV	Ur 12kV
DA1-15B	DA1-15B	LOT No	Uc 12kV	Ur 15kV
DA1-18B	DA1-18B	LOT No	Uc 14.4kV	Ur 18kV

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J MULLIGAN 05/09/2014	 TE Connectivity				
DIMENSIONS: mm		CHK R ULBRYCH					
 TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 1 PLC ± 0.1 2 PLC ± 0.01 3 PLC ± 0.001 4 PLC ± 0.0001 ANGLES ± 1 FINISH -		APVD P FITZGERALD	NAME MV SURGE ARRESTER DA1-xxB RANGE DA1-xxB				
MATERIAL ALL FITTINGS M12, A2 SS		PRODUCT SPEC SEE DATASHEET	APPLICATION SPEC -	SIZE A2	CAGE CODE -	DRAWING NO C=MV-DA1-00429-C	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 of 1	REV A		