Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Penica, John R	**Contact Title**	Mgr Environmental Engineering
Company Unique ID	-	**Response Date**	2014-06-16	**Contact Email**	jrpenica@te.com		
Contact Phone Number	17175923266						

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	4-87977-5	**Amount**	3711.665041	**Version**	-	**Identity**	
Manufacturer Item Name		**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						

Manufacturing Information							
J-STD-020 MSL Rating		**Max Total a Wave Time**		**Ramp Rate**		**Wave Additional Info**	
Classification Temp		**Max Wave Solder Time**	0.0	**Ramp Down Rate**		**Psl Rating Reflow**	
Max Time Within 5		**Psl Rating Wave**		**Package Designator**		**Size**	0.0
Time Above 217		**Reflow Additional Info**		**Preheat Max Temp**		**Terminal Base Alloy**	NAC
Preheat Duration		**bulk Solder Termination**	NAC	**Nbr or Reflow Cycles**		**Terminal Plating**	NAC
Preheat Min Temp		**Nbr of Instances**	0	**Component Temp Spike**		**Shape**	NAC

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Nylon Compound				1.0	3711.665041	mg	
Material	2	PA66-GF25				1.0	3711.665041	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	148.4666	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	222.6999	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	129.90828	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	2282.674	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	927.91626	mg	